

# Eaton XTCE025C10B

Catalog number: XTCE025C10B

Eaton XT IEC contactor, 25A, 220 Vac 50 Hz, 240 Vac 60 Hz, 1NO, 25A, 45 mm, 50-60 Hz, 2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

## General specifications



### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE025C10B

### EAN

4015082771317

### Product Length/Depth

4 in

### Product Height

2 in

### Product Width

3.5 in

### Product Weight

.5 lb

### Compliances

RoHS Compliant CE Marked

### Certifications

UL Listed CSA Certified IEC 60947 EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Frame size

45 mm

### Contact configuration

1 NO

### Coil voltage

220-240 Vac, 50/60 Hz

### Series

XT IEC

### Type

Full voltage non-reversing contactor

### HP rating - max

2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH  
@115,200,230/200,230,460,575 V)

### Continuous ampere rating

25 A

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Operation

Non-reversing

### Amperage Rating

25A

### Number Of Poles

Three-pole

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_C 3D Model Xchange](#)

[XTCE\\_C 2D Drawing Xchange](#)

[XTCE\\_C 2D PDF](#)

[XTCE\\_C AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Global Data Sheet - XTCE025C10B](#)

[Eaton Specification Sheet - XTCE025C10B](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)