

Eaton XTCE025C10T

Catalog number: XTCE025C10T

Eaton XT IEC contactor, 25A, 24 Vac, 50-60 Hz, 1NO, 25A, Frame C, 45 mm, 50-60 Hz, 2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE025C10T

EAN

4015082771362

Product Length/Depth

4 in

Product Height

1.5 in

Product Width

3.5 in

Product Weight

.5070632 lb

Compliances

CE Marked RoHS Compliant

Certifications

UL Listed CSA Certified IEC 60947 EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

45 mm

Contact configuration

1 NO

Coil voltage

24 Vac, 50-60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH
@115,200,230/200,230,460,575 V)

Continuous ampere rating

25 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

25A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_C 3D Model Xchange](#)

[XTCE_C AutoCAD 2D Footprint](#)

[XTCE_C 2D Drawing Xchange](#)

[XTCE_C 2D PDF](#)

Specifications and datasheets

[Global Data Sheet - XTCE025C10T](#)

[Eaton Specification Sheet - XTCE025C10T](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)