

# Eaton XTCE040D00A

Catalog number: XTCE040D00A

Eaton XT IEC contactor, 40A, 110 Vac 50 Hz, 120 Vac 60 Hz, ONO-ONC, 40A, Frame D, 55 mm, 50-60 Hz, 3, 5, 7.5/ 10, 15, 30, 40 hp(1/3PH@115, 200, 230/200, 230, 460, 575 V), Three-pole, , Screw terminals, FVNR



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	XTCE040D00A
<b>EAN</b>	<b>Product Length/Depth</b>
4015082777630	6.25 in
<b>Product Height</b>	<b>Product Width</b>
2.5 in	5 in
<b>Product Weight</b>	<b>Compliances</b>
2.05 lb	CE Marked RoHS Compliant
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Contact configuration

0 NO, 0 NC

### HP rating - max

3, 5, 7.5/ 10, 15, 30, 40 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Operation

Non-reversing

### Amperage Rating

40A

### Number Of Poles

Three-pole

### Coil

110-120 Vac, 50/60 Hz

### Frame size

55 mm

### Coil voltage

110-120 Vac, 50/60 Hz

### Series

XT IEC

### Type

Full voltage non-reversing contactor

### Continuous ampere rating

40 A

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_D 2D PDF](#)

[XTCE\\_D 3D Inventor](#)

[XTCE\\_D 3D Model Xchange](#)

[XTCE\\_D AutoCAD 2D Footprint](#)

[XTCE\\_D 2D Drawing Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE040D00A](#)

[Global Data Sheet - XTCE040D00A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)