

# Eaton XTMC9A10T

Catalog number: XTMC9A10T

Eaton XT IEC mini contactor, 8.80A, 24 Vac, 50-60 Hz, 1NO, 20A, 45 mm mini, 50-60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC mini contactor	XTMC9A10T
<b>EAN</b>	<b>Product Length/Depth</b>
4015080214175	2 in
<b>Product Height</b>	<b>Product Width</b>
2 in	2.5 in
<b>Product Weight</b>	<b>Compliances</b>
.4 lb	RoHS Compliant CE Marked
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Frame size

45 mm - mini

### Contact configuration

1 NO

### Coil voltage

24 Vac, 50-60 Hz

### Series

XT IEC

### Type

Full voltage non-reversing mini contactor

### HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @ 115,200,230/200,230,460,575 V)

### Continuous ampere rating

20 A

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Operation

Non-reversing

### Amperage Rating

8.80A

### Number Of Poles

Three-pole

## Resources

### Brochures

[XT IEC power control 580–2600A vacuum contactors](#)

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTMC AutoCAD 2D Footprint \(mm\)](#)

[XTMC 2D PDF](#)

[XTMC 3D Model Xchange](#)

[XTMC 3D Inventor](#)

[XTMC 2D Drawing Xchange](#)

[XTMC AutoCAD 2D Footprint](#)

### Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

[Contactors Explained](#)

### Specifications and datasheets

[Global Data Sheet - XTMC9A10T](#)

[Eaton Specification Sheet - XTMC9A10T](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)