

Eaton XTMC9A10A

Catalog number: XTMC9A10A

Eaton XT IEC mini contactor, 8.80A, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO, 20A, 45 mm mini, 50-60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



General specifications

Product Name	Catalog Number
Eaton XT IEC mini contactor	XTMC9A10A
EAN	Product Length/Depth
4015080517832	2 in
Product Height	Product Width
2.5 in	2.5 in
Product Weight	Compliances
.2 lb	RoHS Compliant CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

45 mm - mini

Contact configuration

1 NO

Coil voltage

110-120 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing mini contactor

HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115,200,230/200,230,460,575 V)

Continuous ampere rating

20 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

8.80A

Number Of Poles

Three-pole

Resources

Brochures

[XT IEC power control 580–2600A vacuum contactors](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTMC 2D PDF](#)

[XTMC AutoCAD 2D Footprint \(mm\)](#)

[XTMC 2D Drawing Xchange](#)

[XTMC 3D Inventor](#)

[XTMC AutoCAD 2D Footprint](#)

[XTMC 3D Model Xchange](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

[Contactors Explained](#)

Specifications and datasheets

[Global Data Sheet - XTMC9A10A](#)

[Eaton Specification Sheet - XTMC9A10A](#)