

# Eaton XTCE015B10A

Catalog number: XTCE015B10A

Eaton XT IEC contactor, 15A, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO, 15A, Frame B, 45 mm, 50-60 Hz, 1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, Screw terminals, FVNR

## General specifications



**Product Name**  
Eaton XT IEC contactor

**Catalog Number**  
XTCE015B10A

**UPC**  
786689005306

**EAN**  
4015082900557

**Product Height**  
2 in

**Compliances**  
CE Marked RoHS Compliant

**Certifications**  
UL Listed CSA Certified IEC 60947 EN 60947

**Catalog Notes**  
Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Frame size

45 mm

### Contact configuration

1 NO

### Coil voltage

110-120 Vac, 50/60 Hz

### Series

XT IEC

### Type

Full voltage non-reversing contactor

### HP rating - max

1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)

### Continuous ampere rating

15 A

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Operation

Non-reversing

### Amperage Rating

15A

### Number Of Poles

Three-pole

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_B 2D Drawing Xchange](#)

[XTCE\\_B 2D PDF](#)

[XTCE\\_B 3D Inventor](#)

[XTCE\\_B AutoCAD 2D Footprint](#)

[XTCE\\_B 3D Model Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE015B10A](#)

[Global Data Sheet - XTCE015B10A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)