

Eaton XTCE185H22A

Catalog number: XTCE185H22A

Eaton XT IEC contactor, 185A, 100 Vac 50 Hz, 120 Vac 60 Hz, 2NO-2NC, 185A, Frame H, 140 mm, 50-60 Hz, 50, 75, 150, 200 hp (3PH @200, 240, 480, 600 V), Three-pole, Non-reversing, , Screw terminals, FVNR



General specifications

Product Name

Eaton XT IEC contactor

Catalog Number

XTCE185H22A

EAN

4015081363148

Product Length/Depth

6.22047244 in

Product Height

7.08661417 in

Product Width

5.51181102 in

Product Weight

.5070632 lb

Compliances

CE Marked RoHS Compliant

Certifications

UL Listed CSA Certified IEC 60947 EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Contact configuration

2 NO, 2 NC

Coil voltage

100-120 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

50, 75, 150, 200 hp (3PH @200,240,480,600 V)

Continuous ampere rating

185 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

185A

Number Of Poles

Three-pole

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTCE_H 2D PDF

XTCE_H 2D Drawing Xchange

XTCE_H AutoCAD 2D Footprint

XTCE_H AutoCAD 2D Footprint (mm)

XTCE_H 3D Inventor

XTCE_H 3D Model Xchange

Specifications and datasheets

Eaton Specification Sheet - XTCE185H22A

Global Data Sheet - XTCE185H22A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia