

Eaton XTCE007B10E

Catalog number: XTCE007B10E

Eaton XT IEC contactor, 7A, 208 Vac, 60 Hz, 1NO, 7A, Frame B, 45 mm, 60 Hz, 0.25, 0.75, 1/ 1.5, 2, 3, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, , Screw terminals, FVNR



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE007B10E
EAN	Product Length/Depth
4015082765446	3 in
Product Height	Product Width
2 in	3 in
Product Weight	Compliances
.5 lb	CE Marked RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Contact configuration

1 NO

Coil voltage

208 Vac, 60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

0.25, 0.75, 1/ 1.5, 2, 3, 5 hp (1/3PH
@115,200,230/200,230,460,575 V)

Continuous ampere rating

7 A

Frequency rating

60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

7A

Number Of Poles

Three-pole

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_B 2D Drawing Xchange](#)

[XTCE_B 2D PDF](#)

[XTCE_B 3D Inventor](#)

[XTCE_B AutoCAD 2D Footprint](#)

[XTCE_B 3D Model Xchange](#)

Specifications and datasheets

[Global Data Sheet - XTCE007B10E](#)

[Eaton Specification Sheet - XTCE007B10E](#)