

Eaton XTCE015B10B

Catalog number: XTCE015B10B

Eaton XT IEC contactor, 15A, 220 Vac 50 Hz, 240 Vac 60 Hz, 1NO, 15A, Frame B, 45 mm, 50-60 Hz, 1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, , Screw terminals, FVNR

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE015B10B

EAN

4015082900571

Product Length/Depth

3 in

Product Height

2 in

Product Width

3 in

Product Weight

.3 lb

Compliances

CE Marked RoHS Compliant

Certifications

UL Listed CSA Certified IEC 60947 EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Contact configuration

1 NO

Coil voltage

220-240 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)

Continuous ampere rating

15 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

15A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_B 2D Drawing Xchange](#)

[XTCE_B 3D Inventor](#)

[XTCE_B 2D PDF](#)

[XTCE_B AutoCAD 2D Footprint](#)

[XTCE_B 3D Model Xchange](#)

Specifications and datasheets

[Global Data Sheet - XTCE015B10B](#)

[Eaton Specification Sheet - XTCE015B10B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)