

Eaton XTCE015B10T

Catalog number: XTCE015B10T

Eaton XT IEC contactor, 15A, 24 Vac, 50-60 Hz, 1NO, 15A, Frame B, 45 mm, 50-60 Hz, 1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, , Screw terminals, FVNR

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE015B10T

EAN

4015082900625

Product Length/Depth

4.92125984 in

Product Height

2.67716535 in

Product Width

1.77165354 in

Product Weight

.5 lb

Compliances

CE Marked RoHS Compliant

Certifications

UL Listed CSA Certified IEC 60947 EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Frame size

45 mm

Contact configuration

1 NO

Coil voltage

24 Vac, 50-60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

1, 2, 3/ 5, 5, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)

Continuous ampere rating

15 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

15A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_B 3D Inventor](#)

[XTCE_B 2D Drawing Xchange](#)

[XTCE_B 3D Model Xchange](#)

[XTCE_B 2D PDF](#)

[XTCE_B AutoCAD 2D Footprint](#)

Specifications and datasheets

[Global Data Sheet - XTCE015B10T](#)

[Eaton Specification Sheet - XTCE015B10T](#)