

Eaton XV-102-D6-57TVRC-10

Catalog number: XV-102-D6-57TVRC-10

Eaton XV100 basic human machine interface (HMI), 2nd generation CE, XSoft-CoDeSys/Galileo OS, Retentive memory, USB host, RS-232 base unit, CANopen communication, RS-232, RS-485 interface, 5.7 in TFT resistive touch (VGA) display

General specifications



Product Name	Catalog Number
Eaton XV100 basic human machine interface (HMI)	XV-102-D6-57TVRC-10
	EAN
	7640130096752

Product Length/Depth	Product Height
11 in	3 in

Product Width	Product Weight
7.5 in	1.73 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed cULus Listed

Catalog Notes

All 1xx performance class units have 400MHz processor, 64 MB DRAM, 1x10/100 Ethernet, and 1x USB device.

defaultTaxonomyAttributeLabel

Operating system

XSoft-CoDeSys

Galileo

Base unit

Retentive memory, USB host, RS-232

Serial interface

RS-232, RS-485

Bezel

Blank front

Communication

CANopen

Display

5.7 in TFT resistive touch (VGA)

Resources

Brochures

XV and XP Series Operator Interfaces Product Aid - PA04801003E

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

HMI-PLC overview

Specifications and datasheets

Eaton Specification Sheet - XV-102-D6-57TVRC-10

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia