

Eaton XTCE025C10D

Catalog number: XTCE025C10D

Eaton XT IEC contactor, 25A, 550 Vac 50 Hz, 600 Vac 60 Hz, 1NO, 25A, Frame C, 45 mm, 50-60 Hz, 2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE025C10D

EAN

4015082771270

Product Length/Depth

3.425 in

Product Height

3.898 in

Product Width

1.85 in

Product Weight

.9 lb

Warranty

1 year

Compliances

RoHS Compliant CE Marked

Certifications

CSA Certified EN 60947 UL Listed IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

45 mm

Contact configuration

1 NO

Coil voltage

550 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH
@115,200,230/200,230,460,575 V)

Continuous ampere rating

25 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

25A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_C 3D Model Xchange](#)

[XTCE_C AutoCAD 2D Footprint](#)

[XTCE_C 2D Drawing Xchange](#)

[XTCE_C 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCE025C10D](#)

[Global Data Sheet - XTCE025C10D](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)