

# Eaton XV-102-BE-35TQRC-10

Catalog number: XV-102-BE-35TQRC-10

Eaton XV100 basic human machine interface (HMI), Second generation CE plastic housing, XSoft-CoDeSys/Galileo OS, Retentive memory base unit, SmartWire-DT communication, 3.5 in TFT resistive touch (QVGA) display, Standard blank front bezel

## General specifications



### Product Name

Eaton XV100 basic human machine interface (HMI)

### Catalog Number

XV-102-BE-35TQRC-10

### EAN

7640130097599

### Product Length/Depth

11 in

### Product Height

3.5 in

### Product Width

7.5 in

### Product Weight

1.2 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year RoHS Compliant CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

cULus Listed UL Listed

### Catalog Notes

All 1xx performance class units have 400MHz processor, 64 MB DRAM, 1x10/100 Ethernet, and 1x USB device.

## defaultTaxonomyAttributeLabel

### Operating system

XSoft-CoDeSys

Galileo

### Base unit

Retentive memory

### Bezel

Blank front

### Communication

SmartWire-DT

### Display

3.5 in TFT resistive touch (QVGA)

## Resources

### Brochures

[XV and XP Series Operator Interfaces Product Aid - PA04801003E](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[HMI-PLC overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - XV-102-BE-35TQRC-10](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)