

Eaton XV-102-E8-70TWRC-10

Catalog number: XV-102-E8-70TWRC-10

Eaton XV100 basic (HMI), 2nd generation CE, XSoft-CoDeSys/Galileo OS, Retentive memory, USB host, SmartWire-DT base unit, PROFIBUS communication, 7.0 in TFT resistive touch (widescreen) display, Standard blank front bezel

General specifications



Product Name

Eaton XV100 basic human machine interface (HMI)

Catalog Number

XV-102-E8-70TWRC-10

EAN

7640130097636

Product Length/Depth

11 in

Product Height

3.5 in

Product Width

7.5 in

Product Weight

2 lb

Warranty

Eaton Selling Policy 25-000, one (1) year RoHS Compliant CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed cULus Listed

Catalog Notes

All 1xx performance class units have 400MHz processor, 64 MB DRAM, 1x10/100 Ethernet, and 1x USB device.

defaultTaxonomyAttributeLabel

Operating system

Galileo

XSoft-CoDeSys

Base unit

Retentive memory, USB host, SmartWire-DT

Bezel

Blank front

Communication

PROFIBUS

Display

7.0 in TFT resistive touch (widescreen)

Resources

Brochures

[XV and XP Series Operator Interfaces Product Aid - PA04801003E](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[HMI-PLC overview](#)

Specifications and datasheets

[Eaton Specification Sheet - XV-102-E8-70TWRC-10](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)