WIDE RANGE DISTRIBUTION PARALLEL JAW GRIP

- 50% lighter* with one handed grip action
- Holds a wide range of cables:
 - #6 copper to 477MCM ACSR
- Multiple Jaw Styles:
 - Bare Wire ACSR, AAC & CU (Fine Tooth, Gold)
 - Hot Latch (Fine Tooth, Gold)
 - Jacketed Cable (Proprietary Carbide Grit, Silver)
 - EHS Cable (Coarse Tooth, Black)



WIDE RANGE DISTRIBUTION GRIP

Klein Tools' Wide Range Distribution Grips with versatile, one-handed grip holds cable sizes from #6 to 477 ACSR, EHS cable or HDPE-coated cable (tree wire). Grips are 50% lighter than Klein's Cat. No. KT4600 grip. One-handed design makes installation easy. Large opening in the handle accommodates a variety of hooks on hoists, winches and tackle blocks.

- · One-handed design makes installation easier
- 50% lighter patent pending innovative design
- · Holds the widest range of cables:
- #6 Copper to 477 ACSR
- EHS Cable
- HDPE-Coated Cable (tree wire)









INNOVATIVE HOT LATCH CENTERS CABLE

For Professionals
SINCE 1857™





Patent Pending

| Cat. No. | Body Style | Cable Type | Jaw Color | Cable Diameter | Maximum Safe Load | Spring | Hot Latch | Locking Handle | Jaw Length | Approx. Weight |
|-----------------------|---------------|--------------------------------|--------------|--|-------------------------|--------|--------------|-------------------|-------------------|---------------------|
| 16477 | Parallel | Bare Copper, Aluminum, ACSR | Gold | . 0.162" to 0.883" (4.11 to 22.42 mm) | 5,000 lbs (2,268 kg) | • | _ | _ | 3.31" (8.4 cm) | 2.9 lbs (1.3 kg) |
| 16477-20 Hot Latch | | Bare Copper, Aluminum, ACSR | Gold | | | • | • | • | 3.31" (8.4 cm) | 3.2 lb (1.5 kg) |
| 16477-24 | | EHS | Black | | | • | _ | _ | 3.31" (8.4 cm) | 2.9 lb (1.3 kg) |
| 16477-28 | | HDPE- coated cable (tree wire) | Silver | | | • | _ | _ | 3.31" (8.4 cm) | 2.9 lb (1.3 kg) |



See our complete line of Wire Pulling Grips www.kleintools.com

