




Grip for Large Diameter Conductors



This Chicago® Grip is specifically made for ACSR, AAC and copper cabling with larger diameters. These non-returnable grips are special order only. When ordering, please specify exact outside cable diameter, circular mills with strand combination, or the manufacturer's code. Please allow 30 days for delivery.

Specifications

Type:Chicago Grip		Special Features:These grips are special order only, please allow 30 days for delivery, not returnable -- Removable floating jaw held in place by a bolt swaged into the lever arm of the grip, secured by a nut and cotter pin -- Jaw must be removed to insert cable	
Cable Type:ACSR, ACSS, ACSS-TW, AAC		Cable Diameter:0.95" to 1.89" (24.13 to 48 mm)	
Hot Latch:N		Swing Latch:N	
Spring:N		Locking Handle:Y	
Jaw Length:10.75" (27.3 cm)		Maximum Safe Load:25,000 lb (11,340 kg)	
Weight:29.03 lb (13.2 kg)			