



Grip for High Strength Cables 0.55-Inch



Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand. The Chicago style grip was designed for cable sizes from 0.218-Inch to 0.55-Inch (5.5 to 13.9 mm). Double "V" grooves give four-point contact, reducing chance of slipping and providing proper alignment of wire and cable.

Specifications

Type:	Chicago Grip	Application:	Wire Pulling
Cable Type:	Aircraft, EHS, Messenger, Guy Strand	Cable Diameter:	0.218" to 0.55" (5.54 to 13.97 mm)
Hot Latch:	N	Swing Latch:	N
Spring:	Y	Locking Handle:	Y
Jaw Type:	Double V	Jaw Length:	5" (12.7 cm)
Maximum Safe Load:	8000 lb (3629 kg)	Weight:	5.8 lb (2.6 kg)