



High Speed Drill Bit, 17/64-Inch, 118-Degree



Klein Tools Regular-Point 118-degree High-Speed Drill Bits are suitable for general-purpose drilling applications. High-speed bits, in particular, provide a reliable performance in a wide range of materials. They are offered in a variety of different bit sizes and flute lengths for multiple applications.

Specifications

Overall Length:	4.125" (10.5 cm)	Material:	Steel
Bit Diameter:	17/64" (7 mm)	Flute Length:	2.875" (7.3 cm)
Weight:	0.80 oz (22.7 g)		