



High Speed Drill Bit, 25/64-Inch, 118-Degree



Klein Tools Regular-Point 118-degree High-Speed Drill Bits are suitable for general-purpose drilling applications. High-speed bits, in particular, provide a reliable performance in a wide range of materials. They are offered in a variety of different bit sizes and flute lengths for multiple applications.

Specifications

Overall Length:	5.125" (13 cm)	Material:	High Speed Steel
Bit Diameter:	25/64" (10 mm)	Flute Length:	3.75" (9.5 cm)
Weight:	1.6 oz (45.4 g)		