



High Speed Drill Bit, 27/64-Inch, 118-Degree



Klein Tools Regular-Point 118-degree High-Speed Drill Bits are suitable for general-purpose drilling applications. High-speed bits, in particular, provide a reliable performance in a wide range of materials. They are offered in a variety of different bit sizes and flute lengths for multiple applications.

Specifications

Overall Length:	5.375" (13.7 cm)	Material:	High Speed Steel
Bit Diameter:	27/64" (11 mm)	Flute Length:	3.938" (10 cm)
Weight:	2.4 oz (68.0 g)		