




Steel Ship Auger Bit, Screw Point, 1-1/8 x 4-Inch



The deep, open-throat design of the Ship Auger bit clears chips for faster, cleaner cuts. The shank is 7/16-Inch hex to fit 1/2-Inch (13 mm) and larger three-jaw chucks. Used for heavy construction and repair work in mines, on docks and bridges as well as electrical work.

Specifications

| | | | |
|---------------|-----------------|-----------------|--------------|
| Bit Diameter: | 1-1/8" (29 mm) | Shank Diameter: | 0.4" |
| Twist Length: | 4" (10.2 cm) | Overall Length: | 6" (15.2 cm) |
| Weight: | 12.8 oz (363 g) | | |