



Lineman's Pliers, Bolt Thread-Holding



These Lineman's Side-Cutting pliers feature a hinge opening to hold and clean 5/8" (16 mm) pole line and hardware bolts or threaded rods. Cutting knives are induction hardened for long life. The 2000 series blades are designed for heavy-duty cutting of ACSR, screws, nails, and most hardened wire. The high-leverage design provides 46-Percent greater cutting power than other plier designs. Exclusive handle tempering absorbs the "snap" when cutting wire. Pick up these Klein's and feel the difference.

Specifications

Type:	Side Cutting Pliers	Application:	Holds 5/8" (1.6 cm) Pole Line and Hardware Bolts, Threaded Rods; Cuts ACSR, Screws, Nails, and Most Hardened Wire
Overall Length:	9.34" (23.7 cm)	Overall Height:	0.75" (1.9 cm)
Overall Width:	2.06" (5.2 cm)	Material:	Steel
Nose Type:	New England	Jaw Length:	1.594" (4 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.625" (1.6 cm)
Jaw Capacity:	1.43" (3.6 cm)	Knife Length:	Light Blue
Joint Type:	Hot Riveted	Handle Color:	Light Blue
Handle Finish:	Plastic-Dipped	Handle Length:	6.625" (16.8 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.2 lb (0.5 kg)		