



Long Nose Pliers, Insulated, 6-Inch



Klein Tools Insulated Long Nose Side-Cutting pliers are 1000V rated for safety on the job. The long nose is designed for grabbing and looping wire. Dual layer, orange-over-white insulation provides a warning sign that insulation may be compromised. The molded insulation meets or exceeds ASTM F1505-16 and IEC 60900:2012 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	6.9" (17.5 cm)
Material:	Induction Hardened Steel	Jaw Length:	1.969" (5 cm)
Jaw Width:	0.688" (1.7 cm)	Jaw Thickness:	0.375" (1 cm)
Jaw Capacity:	1.72" (4.4 cm)	Point Diameter:	0.094" (0.24 cm)
Cutting Knives:	Standard	Knife Length:	0.572" (1.5 cm)
Cut Style:	Side-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	4.422" (11.2 cm)	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight:	4.8 oz (136 g)