



Pliers, Long Nose Side-Cutters, Insulated, 7-Inch



Klein Tools Insulated Long Nose Side-Cutting pliers are 1000V rated for safety on the job. The long nose is designed for grabbing and looping wire. Dual layer, orange-over-white insulation provides a warning sign that insulation may be compromised. The molded insulation meets or exceeds ASTM F1505-16 and IEC 60900:2012 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

| | | | |
|--------------------------|---|------------------------|---------------------------------|
| Type: | Long Nose Side Cutting Pliers | Application: | For Work Near Energized Sources |
| Special Features: | Flame Retardant and Impact Resistant Handle | Overall Length: | 7.37" (18.7 cm) |
| Material: | Induction Hardened Steel | Jaw Length: | 2.43" (6.2 cm) |
| Jaw Width: | 0.688" (1.7 cm) | Jaw Thickness: | 0.375" (1 cm) |
| Point Diameter: | 0.094" (0.24 cm) | Cutting Knives: | Standard |
| Knife Length: | 0.572" (1.5 cm) | Cut Style: | Side-Cutting |
| Joint Type: | Hot-Riveted | Handle Color: | Orange |
| Handle Finish: | 2-Layer Insulation | Insulated: | Yes |
| Standard: | IEC 60900 and ASTM F1505 | Weight: | 4.8 oz (136 g) |