



Diagonal Cutting Pliers, Insulated, Heavy-Duty, 7-Inch



These Insulated Diagonal-Cutting pliers have dual layered grips that are flame retardant, impact resistant, and rated for 1000-volts. They feature a heavy-duty tapered nose design with induction hardened cutting knives for durability. They are made of forged steel and have a hot-riveted joint for smooth action and no handle wobble.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	7.67" (19.5 cm)
Material:	Induction Hardened Steel	Nose Type:	Tapered
Jaw Length:	1" (2.5 cm)	Jaw Width:	0.969" (2.5 cm)
Jaw Thickness:	0.5" (1.3 cm)	Jaw Capacity:	1.1" (2.8 cm)
Cutting Knives:	Standard	Cut Style:	Diagonal-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length:	6" (15.2 cm)
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight:	11.2 oz (318 g)		