



Lineman's Pliers, Crimping, 9-Inch



These Lineman's Pliers feature a built-in crimper for non-insulated connectors. Heavy-duty cutting knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting power. The dual-material Journeyman handles are more comfortable and durable than other handles.

Specifications

| | | | |
|------------------------|---|-----------------------|---|
| Type: | Heavy Duty High Leverage Side Cutting/Crimping Pliers | Application: | ACSR, Screws, Nails, Most Hardened Wire; Crimps Noninsulated Connectors, Lugs and Terminals |
| Overall Length: | 9.55" (24.3 cm) | Material: | Steel |
| Nose Type: | New England | Jaw Length: | 1.594" (4 cm) |
| Jaw Width: | 1.25" (3.2 cm) | Jaw Thickness: | 0.625" (1.6 cm) |
| Jaw Capacity: | 1.43" (3.6 cm) | Knife Length: | Light Blue/Black |
| Handle Color: | Light Blue/Black | Handle Finish: | Journeyman™ Dual-Material |
| Handle Length: | 7.375" (18.7 cm) | Insulated: | No |
| Tether Capable: | No | Weight: | 1.1 lb (0.5 kg) |