



Insulated Screwdriver, #2 Square, 4" Shank



Klein insulated tools combine excellent functionality along with reduction of risk of injury where a tool might make contact with an energized source with voltage up to 1000 volts. Two layers of insulation provide protection against electric shock. Clearly marked with the official 1000-volt rating symbol. Round shank with square-recess tip.

Specifications

Application:	For Work Near Energized Sources	Special Features:	Flame Retardant and Impact Resistant Handle
Tip Type:	Square	Magnetic:	No
Tip Size:	#2	Shank Type:	Round
Shank Length:	4" (10.2 cm)	Material:	Induction Hardened Steel
Insulated:	Yes	Handle Material:	High-Dielectric Plastic
Handle Color:	Black	Color Code:	Red
Overall Length:	8.313" (21.1 cm)	Standard:	IEC 60900 and ASTM F1505
Type:	Recessed	Weight:	3.2 oz (91 g)