

Klein canvas buckets and accessories have been recognized for decades for their durability and dependability. They are built for strength to handle professional wear and tear.

For Professionals... Since 1857™



# **Load Rated Canvas Buckets**

Durable, straight-wall and tapered-wall buckets are made of heavy-duty canvas.

#### AWARNINGS:

- Inspect for damage before each use.
- Remove from service if bucket shows signs of wear.
  - Never exceed the working load limit.

### Leather-Bottom Buckets

#### Additional Features:

KLEIN TOOL

- Leather reinforced bottom
- Leather cuff extends 3" (76 mm) up the side
- High-density polyethylene top ring for strength and chemical resistance
- Inside pocket measures 8" x 8" (203 mm x 203 mm)
- Cat. Nos. 5104 and 5104S feature a web strap that extends down the side of the bucket
- Cat. No. 5104VT features top with Velcro® brand fasteners and multiple attachment loops for easy access and storage
- Load Rated 100 lbs. (45 kg)

Cat. No.	Diameter	Height	Material	Special Features	Weight
5104	12" (304.8 mm)	17" (431.8 mm)	No. 4 Canvas	—	2.7 lbs. (1.22 kg)
5104S	12" (304.8 mm)	17" (431.8 mm)	No. 4 Canvas	Swivel Snap (Cat. No. 2012)	2.9 lbs. (1.32 kg)
5104VT	12" (304.8 mm)	17" (431.8 mm)	No. 1 Canvas	VELCRO® Closure	3.0 lbs. (1.36 kg)

VELCRO® is a registered trademark of Velcro Industries B.V.

### Wide Opening Straight-Wall Buckets

#### **Additional Features:**

- Black molded polypropylene bottom with drain holes ٠
- Web strap extends down the side of the bucket
- · High-density polyethylene top ring for strength and chemical resistance

Cat. No.	Diameter	Height	Material	Special Features	Load Rating	Weight
5109	12" (304.8 mm)	15" (381.0 mm)	No. 6 Canvas	_	75 lbs. (34 kg)	2.1 lbs. (0.95 kg)
5109P	12" (304.8 mm)	15" (381.0 mm)	No. 6 Canvas	One 8" x 8" (203.2 x 203.2 mm) Inside Pocket	75 lbs. (34 kg)	2.1 lbs. (0.95 kg)
5109S	12" (304.8 mm)	15" (381.0 mm)	No. 6 Canvas	Swivel Snap (Cat. No. 2012)	75 lbs. (34 kg)	2.4 lbs. (1.09 kg)
5109PS	12" (304.8 mm)	15" (381.0 mm)	No. 6 Canvas	One 8" x 8" (203.2 x 203.2 mm) Inside Pocket and Swivel Snap (Cat. No. 2012)	75 lbs. (34 kg)	2.4 lbs. (1.09 kg)
5109SLR	12" (304.8 mm)	15" (381.0 mm)	No. 4 Canvas	_	150 lbs. (68 kg)	6.0 lbs. (2.72 kg)



5109SLR

260

#### www.kleintools.com

RATED 100 lbs. (45 kg)

51045 DID LIMIT BLBS (45kg) 00 LBS (45

5104S

5104VT

5109S

### **Canvas Buckets & Lineman Accessories**



### **Heavy Duty Top Closing Buckets**

- Additional Features:
- No. 1 canvas
- Top of bucket zips closed
- 14" (356 mm) diameter accommodates standard 5 gallon bucket
- Web strap extends down the side of the bucket
- Leather reinforced bottom extends 3" (76.2 mm) up the side
- Durable steel rim
- Load Rated 150 lbs. (68 kg)



Holds 5 gallon bucket (not included)

Cat. No.	Diameter	Height	Weight
5104CLR17	14" (355.6 mm)	17" (431.8 mm)	6.7 lbs. (3.04 kg)
5104CLR22	14" (355.6 mm)	22" (558.8 mm)	7.0 lbs. (3.18 kg)
010102.122		(000101111)	110 1201 (0110 lig)

AWARNING: Completely close top before each use

# 150 lbs. (68 kg) OAD LIMIT LOAD LIMIT 150 LBS (68kg) 150 LBS (68kg) Inspect before each **Spect helow**

5104CLR17

5104CLR22

### **Canvas Bucket with Connection Points**

- Six small D-rings sewn to the interior of the bucket provide secure connection points for tethers
- Extra large hook to fit onto oversized rigging equipment
- Leather reinforced bottom
- High-density polyethylene top ring provides strength and chemical resistance
- 8" (203.2 mm) x 8" (203.2 mm) inside pocket
- Load Rated 100 lbs. (45 kg)



Cat. No.	Diameter	Height	Weight
51040CT0	12" (304.8 mm)	15" (381.0 mm)	6.0 lbs. (2.72 kg)





51040CT0



### **Canvas Buckets & Lineman Accessories**

## **Canvas Buckets**

### **Straight-Wall Buckets**

- No. 6 canvas
- Black molded polypropylene bottom
- Rope handle



### **Tapered-Wall Buckets**

- No. 6 canvas
- Black molded polypropylene bottom
- Rope handle



Cat. No.	Diameter	Height	Special Features	Weight
5106	9" (228.6 mm)	14" (355.6 mm)	_	1.5 lbs. (0.68 kg)
5106P	9" (228.6 mm)	14" (355.6 mm)	Two 7" x 7" (177.8 x 177.8 mm) Inside Pockets	1.6 lbs. (0.73 kg)
5106S	9" (228.6 mm)	14" (355.6 mm)	Swivel Snap (Cat. No. 2012)	1.8 lbs. (0.82 kg)

Cat. No.	Top Diameter	Bottom Diameter	Height	Special Fea- tures	Weight
5113	12" (304.8 mm)	9" (228.6 mm)	13" (330.2 mm)		1.6 lbs. (0.73 kg)
5113S	12" (304.8 mm)	9" (228.6 mm)	13" (330.2 mm)	Swivel Snap (Cat. No. 2012)	1.8 lbs. (0.82 kg)

### **Heavy-Duty Tapered-Wall Buckets**

- No. 4 canvas
- Black molded polypropylene bottom
- Rope handle
- Riveted leather glove strap
- Equipped with Cat. No. 2012 swivel snap hook



Cat. No.	Top Diameter	Bottom Diameter	Height	Pockets	Weight
5103S	12" (304.8 mm)	9" (228.6 mm)	12" (304.8 mm)	-	2.0 lbs. (0.91 kg)
5171PS	12" (304.8 mm)	9" (228.6 mm)	12" (304.8 mm)	4 Outside Pockets	2.2 lbs. (1.00 kg)
5172PS	12" (304.8 mm)	9" (228.6 mm)	12" (304.8 mm)	15 Inside Pockets	2.4 lbs. (1.09 kg)

### **Vinyl Bucket Top**

- Top cover for canvas bucket designed to keep the elements out and tools securely inside
- Compatible with Klein Tools 5104 and 5109 series buckets
- Attaches with Velcro<sup>®</sup>
- Includes safety strap loop to ensure connection to bucket
- Bucket not included

Cat. No.	Diameter	Height	Weight		
51TOP	12-1/2" (317.5 mm)	3-1/2" (88.9 mm)	6.4 oz. (181 g)		
VELCBO® is a registered trademark of Velcro Industries B V					





51T0P

#### www.kleintools.com

### **Canvas Buckets**

### **Oval Bucket with Pockets**

- No. 6 canvas
- Black molded polypropylene bottom
- Sisal-rope handle
- Tripod suspension rope for greater stability
- Equipped with Cat. No. 2012 swivel snap hook

Cat. No.	Length	Width	Height	Pockets	Weight
5144S	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	15 Inside	2.2 lbs. (1.00 kg)
5152S	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	26 Inside 15 Outside	2.5 lbs. (1.13 kg)





5152S

5144

### Aerial-Basket Oval Bucket with 15 Interior Pockets

- No. 6 canvas
- Black molded polypropylene bottom
- Two nylon 66 polymer hooks (Cat. No. 5144H) included with Cat. No. 5144

Cat. No.	Length	Width	Height	Pockets	Special Features	Weight
5144	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	15 Inside	Two Hooks (Cat. No. 5144H)	2.0 lbs. (0.91 kg)
5144B	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	15 Inside Pockets	—	1.5 lbs. (0.68 kg)

### Hard Body Oval Buckets

- Cat. Nos. 5144BHB and 5144BHHB are constructed of high density polyethylene
- Cat. No. 5144BHB140S is constructed of rugged denier polyester to resist wear and tear on the jobsite
- Black molded polypropylene bottom with drain holes

**Kick Stand** on back of

• Cat. No. 5144H hooks sold separately







Cat. No. 5144BHB

Cat. No.	Color	Length	Width	Height	Pockets	Handle	Weight
5144BHB	Orange	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	14	No	2.0 lbs. (0.91 kg)
5144BHHB	Orange	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	14	Yes	2.0 lbs. (0.91 kg)
5144BHB140S	Black	14" (355.6 mm)	7" (177.8 mm)	10" (254.0 mm)	29	Yes	3.0 lbs. (1.36 kg)

inside of

Height

10" (254.0 mm)

Pockets

15 Inside

### Hard Body Oval Bucket with Knife Sheath

- Includes leather skinning knife sheath and 14 other interior pockets
- Orange, non-conductive plastic exterior maintains bucket shape
- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite **Knife Sheath**

Width

7" (177.8 mm)

· Black molded polypropylene bottom with drain holes

Length

14" (355.6 mm)

Cat. No. 5144H hooks sold separately

Color

Orange

Cat. No.

5144HBS



Weight

2.0 lbs. (0.91 kg)

Handle

Yes



#### www.kleintools.com



### **Canvas Buckets**

### **Canvas Tapered-Bottom Bag**

- No. 10 canvas
- Two pockets are provided for small parts
- Bottom is tapered so parts will stay in center
- Equipped with a snap for hanging

Cat. No.	Diameter	Depth	Weight
5143	6-1/2" (165.1 mm)	8" (203.2 mm)	4.8 oz. (136 g)



5143

### Line-Hose Bag

- No. 6 canvas with top ring and molded bottom
- Large enough to accommodate several pieces of hose
- Can also be used to raise protective rubber blankets that are rolled
- Leather cuff extends 3" (76.2 mm) up the side
- Polypropylene rope handle is reinforced with leather

Cat. No.	Diameter	Depth	Weight
5110-48	7" (177.8 mm)	48" (1219.2 mm)	1.9 lbs. (0.86 kg)



- Made of tough No. 4 canvas.
- Heat-resistant, hard leather bottom.
- Cat. No. 5471FR is made of flame-retardant No. 4 canvas which meets the performance requirement of NFPA -701.
- Web loop for sliding over belt.

			IFR 5471FR	5471 5471
Cat. No.	Diameter	Front Depth	Back Depth	Weight
5471	2-1/2" (63.5 mm)	12" (304.8 mm)	15-1/2" (393.7 mm)	4.0 oz. (113 g)
5471FR	2-1/2" (63.5 mm)	12" (304.8 mm)	15-1/2" (393.7 mm)	4.0 oz. (113 g)



## **Lineman Accessories**

### **Aerial Aprons**

- Includes: ten hand tool pockets, two pouches, hammer loop and two drill bit holders (Cat. Nos. 51829 and 51829M)
- Two pouches reinforced with heavy duty rivets
- Cat. No. 5144H hooks sold separately
- Cat. No. 51829MHS includes hot stick pocket
- Sewn-in magnet conveniently holds nuts, bolts and other small metal objects







Cat. No.	Color	Width	Height	Pockets	Magnet	Weight
51829	Orange	24" (609.6 mm)	23" (584.2 mm)	18	No	4.0 lbs. (1.81 kg)
51829M	Orange	24" (609.6 mm)	23" (584.2 mm)	18	Yes	4.0 lbs. (1.81 kg)
51829MHS	Orange	32" (812.8 mm)	27-1/2" (698.5 mm)	16	Yes	4.0 lbs. (1.81 kg)

### **Swivel Snap Hook**

- This is NOT an occupational protective hook. NOT for human support
- Bronze swivel snap hook made for use on canvas buckets
- Maximum safe load 150 lbs. (68 kg)



### Hook for Aerial-Baskets and Buckets

- All weather, durable, nylon 66 polymer
- Most manufacturers' aerial basket trucks

Weight

4.8 oz. (136 g)

accommodate bucket hook Replacement hook for 5144 Series Baskets and Buckets except 5144S

NOT FOR HUMAN SUPPORT



5144H

66141KIT

Cat. No.	Length	Width	Weight	Cat. No.
2012	4-3/8" (111.1 mm)	1-5/8" (41.3 mm)	4.5 oz. (128 g)	5144H

### Pole Pick and Pouch

- Helps determine the condition of a utility pole before climbing
- Extra sharp point for piercing many types of wood poles
- Smooth Comfordome handle fits the palm of the hand comfortably
- Cat. No. 66141KIT includes pole pick (Cat. No. 66141) and pouch (Cat. No. 66141P)

Cat. No.	Includes	Overall Length	Weight
66141KIT	Pole Pick and Pole Pick Pouch	15-5/16" (388.9 mm)	6.4 oz. (181 g)



• For use where a running loop wrap around pole is desired

Nylon web stitched with nylon thread

Cat. No.	Rated Capacity Choke Hitch	Rated Capacity Basket Hitch	Overall Length	Width	Weight	AWARNING: This is NOT an occupational
5606	3000 lbs. (1361 kg)	4700 lbs. (2115 kg)	39" (990.6 mm)	2" (50.8 mm)	1.3 lbs. (0.59 kg)	protective device. NOT for human support.

5606