



#2 Insulated Screwdriver with 7-Inch Shank



Klein insulated tools combine excellent functionality along with reduction of risk of injury where a tool might make contact with an energized source with voltage up to 1000 volts. Two layers of insulation provide protection against electric shock. Clearly marked with the official 1000-volt rating symbol. Round shank with square-recess tip.

Specifications

| | | | |
|------------------------|---------------------------------|--------------------------|---|
| Application: | For Work Near Energized Sources | Special Features: | Flame Retardant and Impact Resistant Handle |
| Tip Type: | Square | Magnetic: | No |
| Tip Size: | #2 | Shank Type: | Round |
| Shank Length: | 7" (17.8 cm) | Material: | Induction Hardened Steel |
| Insulated: | Yes | Handle Material: | High-Dielectric Plastic |
| Handle Color: | Black | Color Code: | Red |
| Overall Length: | 11.313" (28.7 cm) | Standard: | IEC 60900 and ASTM F1505 |
| Type: | Recessed | Weight: | 3.2 oz (91 g) |