

Project Name

Location

Prepared By



## SATCO S39836

9.8A19/OMNI/220/LED/30K

### Notes

[www] 06-11-2022 21:35:53

### General

Status	Active
Watts	9.8W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80
Lumens	800L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Power Factor	0.81
Operating Temperature	-25C (-13F) to +45C (+113F)

### Physical

MOL	4.33
MOD	2.36
Weight (lb.)	0.06

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

### Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2389075
CA T20 / T24 Rationale	Non-Compliant - Not 82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp