

# **GET MORE DONE WITH ONE TOOL**

Ultimate Versatility in Cutting

### NEW

# INTERCHANGEABLE CUTTING JAWS

FOR EK628 AND EK425 6-TON BATTERY TOOLS

CJ-ACSR1 / CJ-CUAL

Cutting and crimping solutions with one tool

### Capacity

CJ-ACSR1

477 kcmil Pelican ACSR
5/16" Guy Strand (EHS)
3/8" Guy Strand (HS)

CJ-CUAL

600 kcmil Copper
(Cu) & Aluminum (Al)

Multi-Functional

- Interchangeable jaws reduce
- number of tools required for a job
- Compatible with "X" and "L" Series Gator® Tools

### Easy to Use

- Simply select, change, and cut
- Patented quarter turn locking pin for easy jaw installation and removal

### **Ergonomic**

- Maneuverability and reduced weight provide improved working posture
- Open-mouth jaw and single trigger eliminates need for two-handed operation



# **GET MORE DONE WITH ONE TOOL**

INTERCHANGEABLE CUTTING JAWS FOR EK628 AND EK425 6-TON BATTERY TOOLS

CJ-ACSR1 / CJ-CUAL

### Capacity

Up to 477 kcmil Pelican
Up to 5/16" Guy Strand (EHS)
Up to 3/8" Guy Strand (HS)



Hardened Blade
Produce clean, smooth cuts

## Interchangeable Jaws Quickly and easily change jaws



#### ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION	
CJ-CUAL	8223	CU/AL CUTTER JAW ASSEMBLY	
CJ-ACSR1	08224A	ACSR CUTTER JAW ASSEMBLY	

#### ADDITIONAL JAW SETS AVAILABLE











CJD30

CJK

UJX

JAW SET	DESCRIPTION	
CJBC	Cutting Jaws for disposable locks.	
CJD3BG	Crimping jaws with D and BG die grooves. Accepts W dies	
CJD3	Crimping jaw with single D die groove - Snub Nose. Accepts W dies	
CJD30	Crimping jaw with D and O grooves	
CJK	Crimping jaw with Kearney O die grooves	
CJXPJ	Crimping jaw with Nicopress X, P, and J die grooves	

#### **SPECIFICATIONS**

	CJ-ACSR1	CJ-CUAL
CAPACITY:	477 kcmil Pelican ACSR 5/16" Guy Strand (EHS) 3/8" Guy Strand (HS)	600 kcmil Cu/Al
LENGTH:	5.72 in	5.47 in
WEIGHT:	2.45 lbs	2.35 lbs

 $\textit{Makita}^{\circledast} \textit{ is a registered trademark of Makita Corporation}.$ 

