

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L3 and L3R.

CONSTRUCTION

Antique bronze, oil-rubbed bronze, brushed nickel, white and black finishes are one piece aluminum open reflectors with integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.


Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.

WARRANTY

1-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application.

Specifications subject to change without notice.



3" Finishing Trim



BAFFLE SHALLOW

Narrow Flange


Example: 3B1

Specifications

Height: 4-3/4 (12.1)

Lamp opening: 3-1/2 (8.9) Diameter: 4-7/8 (12.4)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION For shortest lead times, configure product using **bolded options**.

		Tot shortest lead airies, comigate product using polace options.			
3B1	3B1				
Series	Finish				
3B1	(blank) TRMW W MW ORB	Black baffle, white flange Black baffle, matte white flange White baffle Matte white baffle Oil-rubbed bronze baffle			

Housing Compatibility: Housing and trim ordered separately.						
Application	Source	Maximum wattage	Housing			
		35 PAR20				
IC	Incandescent	50 PAR201	L3, L3R			
		50 R201				
Non-IC	Incandescent	50 PAR20	L3, L3R			

Notes

1 White baffle (3B1W) only.

DOWNLIGHTING 3B1

