TRACK LIGHTING NOVEMBER 2020

yourbeauty



Detox Market. New York, New York, USA Architect: Suulin Architects



Table of Contents

VER	SATILE TRACK FIXTURES
6.	FLEX
10.	DINE
TRA	CK HEADS
12.	DELTA, APOLLO, SORA
14.	FLIGHT SERIES
16.	TEARDROP SERIES
19.	ATF7630
20.	ATF74
22.	ATF75
24.	FOCUS SERIES
28.	WALL WASH
30.	TRACK HEADS & ADAPTERS
TRA	СК
31.	TRACK
32.	RIGIDITY
33.	TRIMLESS
34.	TRACK SYSTEMS















GO SMART

Make any dimmable fixture smart by connecting the circuit to Liteline's new OnCloud DIMMER. It connects to your Wi-Fi through the WiZ app on your smartphone or tablet.

LC-CRTL-DIM-1



Works with

SmartThings

COMPATIBLE WITH







Liteline's robust lineup of track fixtures provides flexible lighting solutions for both residential and commercial applications, including but not limited to art galleries, retail and higher education. With a range of track compatibility including Halo and Juno, a variety of outputs, color temperatures, beam angles and accessories, our track collection can accommodate your project's needs.

Manage lighting for multiple venues from the mobile or desktop application.

> Create presets to automatically dim the lights to better suit the time of day. Easily go from a bright lunch setting to a dim dinner time setting.



NO HUB NEEDED



MULTI-USER



MULTI-LOCATION

Works with Siri Shortcuts





FLEX ONE BODY, FIVE MOUNTING OPTIONS

This A-Line product is the perfect solution for creating a unified look when working with multiple ceiling types. The high output capabilities, beam angles and color temperatures make Flex a great choice for commercial, hospitality, higher education and healthcare applications. The slim body design of Flex having five mounting options and seven accessories, creates endless possibilities for your commercial project.







ACCESSORIES

FLX15








FLX22





andela Distribution	Beam Details					Zon	al Lumen S	ummary
169 165 180 1.165 160 100 100 100 100 100 100 100	D 4' 8' 12' 16' 20'	Lux 3115 779 346 195 125	FC 289 72 32 18 12	L 2.8' 5.6' 8.4' 11.2' 14'	W 2.8' 5.6' 8.4' 11.2' 14'	Zone 0-30 0-40 0-60 60-90 70-100 90-120 0-90 <u>90-180</u> 0-180	Lumens 834.0 1271.0 1866.0 258.0 143.0 69.3 2125.0 119.0 2321.0	% Luminaire 35.93% 54.76% 80.40% 6.16% 2.99% 91.56% 5.13% 100.00%

FLX38





25°


40°


60

FINISH WHITE (WH) BLACK (BK) SILVER (SL)

CRI

90






 Ordering Guide
 Color Temperature
 Beam Angle
 Mounting
 Finish

 Connector Type

FLX38-3040 : FLEX FIXTURE, 38W, 3000 K, 40° BEAM SPREAD











Looking to create a cozy and inviting experience? The DINE Series offers Dim-to-Warm capabilities, a range of beam angles and a designer inspired finish to set the mood for your hospitality application, providing a warm and precise cone of light over dining tables. DINE also gives you on-site flexibility of light cut-off with an adjustable screw, allowing for zero glare.





- ACCESSORIES -----



1" SN00T







T-LEDDNG



Mounting	Track Connector	Snoot Size	Finish
-	LEDDNG	-]-
T : Track TP : Track Pendant	Blank : For all other mounting options except track	SN1 : 1" Snoot SN2 : 2" Snoot	WH : White BK : Black
SP : Pendant	A:A-Line	SN4: 4" Snoot	
RP : Recessed Pendant	C:C-style H:H-style		
SF : Surface	L:L-style		
RF : Recessed	LL : Liteline		
Surface	P2 : Powergear 2-circuit		
MP : Monopoint	P3 : Powergear 3-circuit		

Color swatches may not be exact, contact rep for sample. Due to our continued efforts to improve our products, product specifications are subject to change without notice. Refer to liteline.com for up to date specifications.












FINISH

APOLLO, DELTA, & SORA


The APOLLO and SORA fixtures feature updated integrated LED technology in a traditional track style. The newest member of this fixture family, DELTA, has a slender profile and the addition of a 40 K color temperature option. Their competitive price point, compact size, 358-degree rotation and 90-degree tilt make them ideal for residential and light commercial applications.

DELTA: DA2010





SORA: S01008




Ordering Guide Connector Type Color Temp. Finish Beam Angle SO1008 Blank : A-Line 27:2700 K **38:**38° WH : White BK : Black LL : Liteline 30:3000 K H:H-style SL: Silver L:L-style Highlighted option denotes quick ship.

APOLLO: A01008




Interview			
	WHITE (WH)	BLACK (BK)	SILVER (SL)
BEAM ANGLES	CRI		
	90		

RATINGS



A01008-3038-WH: 8W APOLLO TRACK FIXTURE, 3000 K, 38° BEAM SPREAD, WHITE



DELIVERED

Up to 605 Im

27 K 30 K


CCT


Polar Candela Distribution		Beam Details					al Lumen S	ummary
150 165 150 125 126 126 120 105 90 90		ł]		Zone 0-30 0-40 0-60 60-90	Lumens 398.8 479.2 544.9 24.7	% Lum 6 inaire 96.3% 79.7%
75	<u>D</u> 4'	Lux 619	FC 57	L 2.9'	<u>W</u> 2.9'	70-100 90-120	18.4 12.9	0.7% 4.1%
60 60	8'	155	14	5.8	5.8'	0-90	569.6	93.1%
	12' 16'	69 39	6 4	8.7 11.6	8.7 11.6	90-180 0-180	31.4 601.0	2.1%
39.9°	20'	25	2	14.5'	14.5'			5.2% 0.0%

DA2010-3038-80WH: 10W DELTA TRACK FIXTURE, 3000 K, 38° BEAM SPREAD, 80 CRI, WHITE


	Candela Distribution		Bea	m Dei	tails		Zona	al Lumen S	ummary
sh	150 165 160 165 150 150 150 150 150 105 105	_	Ë	3]		Zone 0-30 0-40 0-60 60-901	Lumens 3163 4914 7537 83	% Luminaire 1.79% 9.40% 5.75% 18.41%
	111111	 	Lux 1046	FC 97	 3'		70-100	1321	3.28%
nite		8'	261	24	5.9'	5.9'	90-120	69.6	7.00%
	45	12'	116	11	8.9'	8.9'	0-90	9369	4.16%
ck	30 / 30	16'	65	6	11.9'	11.9'	90-180	109	10.97%
er	40.7°	20'	42	4	14.8'	14.8	0-1809	94	100.00%

DA2010-3038-WH: 9W DELTA TRACK FIXTURE, 3000 K, 38° BEAM SPREAD, 90 CRI, WHITE





S01008-3038-WH:	8W SORA	TRACK FIXTURE	3000 K	38° F	SEAM SPREAD	WHITE
001000-0000-Will.	011 0011-	INAUNTIMONE	, 0000 IV,	00 L	JEAN OF HEAD,	*******






FLIGHT SERIES



Point perfect! With beam angles as tight at 6°, the Flight Series is the ideal choice for emphasizing focused light from a distance. Its small body profile, three finish choices and wide range of beam angles make Flight the recommended fixture for your residential projects.


ATF7610






ATF7610-DTW






FLIGHT SERIES




ATF7610-DTW40 : LED TRACK HEAD, 10W, 3000 K, 40° BEAM SPREAD




Beam 0.9ft 1.8ft	0.98
1.811	1.01
2,78	2,78
3,61	3,61
4.5ft	4.61
5.411	5.51
	3.6ft 4.5ft

TEARDROP SERIES

The Teardrop track series is one of our most powerful lineups, with delivered lumens of up to 3000. The unique body shape, wide range of color temperature options, and accessories allow for greater control to set the mood for your commercial space.




ATF8514



	Connector Type		Color Temp.	Beam Spread	CRI	Finish
	- /	ATF8514 -			-	
\sim	Blank : A-Line		27:2700 K	40:40°	90:90+CRI	WH: White
$\langle \rangle \rightarrow$	LL : Liteline		30:3000 K	15:15°		BK : Black
=\/	H:H-Style		35:3500 K			SL : Silver
UICKSHIP	L:L-Style		50:5000 K			
7-DAY	P2: 2-circuit Powergear					
	P3: 3-circuit Powergear					


ATF8522








ATF8514-3025-90: LED TRACK HEAD, 14W, 3000 K, 25° BEAM SPREAD, 90 CRI




ATF8522-3025-90: LED TRACK HEAD, 22W, 3000 K, 25° BEAM SPREAD, 90 CRI


Zonal Lumen Summary						
Zone	Lumens	% Luminaire				
0-30	1,184.5	73.9%				
0-40	1,392.6	86.9%				
0-60	1,552.2	96.9%				
60-90	49.8	3.1%				
0-90	1.602.0	100%				



_	Center Beam FC	Beam	Width
.3ft	2,133 fc	0.7R	0.78
.71	495 fc	1.50	1.50
.on	225 fc	2.38	2,38
.311	128 fc	3.00	3,08
.78	80.3 fc	3.80	3,88
08	56.3 fc	4.5ft	4.50









ATF8536









FINISH



Ordering Guide



ATF8536-3040-90: LED TRACK HEAD, 36	W, 3000 K, 40° BEAM SPREAD, 90 CRI




ATF7630





ATF7630

The ATF7630 is a 30W LED track fixture that offers a powerful lumen package of up to 2200 lumens. Pair it with a variety of accessories including barn doors for tailored beam angles.




ATF7630-3029: LED TRACK HEAD, 30W, 3000 K, 29° BEAM SPREAD

Polar Candela Distribution		Bea	m Det	ails		Zon	al Lumen S	ummary
135 135 135 100 100 70 70 70 45	D 4' 8' 12'	Lux 4353 1088 484	FC 404 101 45	L 2.2' 4.5' 6.7'	W 2.2' 4.5' 6.7'	Zone 0-30 0-40 0-60 60-90 70-100 90-120 0-90 90-180	Lumens 1,994.1 2,081.7 2,131.2 43.6 26.8 7.8 2,174.8 20.8	% Luminaire 90.8% 94.8% 97.1% 2% 1.2% 0.4% 99.1% 0.9%
30 1 0 1 30 31.3°	16' 20'	272 174	25 16	9 11.2	9' 11.2'	0-180	2,195.6	100%


ATF74 SERIES

This track series is a versatile solution for your commercial applications. It is available in both 15W and 25W, a wide range of beam angles, a commanding 2250 lumens delivered and Dim-to-Warm capabilities on select models.









Connector Type		Beam Spread	Finish
	ATF7415 DTW		
Blank : A-Line		38:38°	WH : White
H: H-Style		00100	BK : Black
L: L-Style			
P2 : 2-circuit Powergear			
P3: 3-circuit Powergear			

ATF7415



Ordering Guide Beam Spread CRI / Finish Color Temp. Connector Type Zone 0-30 0-40 0-60 60-90 70-100 90-120 0-90 0-90 Lumen: 989 1091 1155 36.4 27.0 15.0 1192 Luminaire 80.87% 89.21% 94.44% 2.98% 2.21% 1.23% 97.47% 2.54% 100% ATF7415 D Lux FC L W 4' 1881 175 2.5' 2.5' 8' 470 44 5.1' 5.1' 12' 209 19 7.6' 7.6' 16' 118 11 10.2' 10.2' 20' 75 7 12.7' 12.7' Blank : A-Line 30:3000 K -38:38° 90WH: 90 CRI, White LL : Liteline **35 :** 3500 K **15 :** 15° 90BK: 90 CRI, Black 90-180 H : H-Style P2 : 2-circuit Powergear 40:4000 K 20:20° QUICKSHIF 7-DAY 60:60° P3: 3-circuit Powergear Highlighted option denote quick ship.

ATF7425



	Connector Type		Color Temp.	Beam Spread	Finish
		ATF7425	·		
\sim	Blank : A-Line		30: 3000 K	38:38°	WH : White
$ \leq \Sigma $	LL : Liteline		35 : 3500 K	15:15°	BK : Black
	H: H-Style		40:4000 K	25:25°	SL : Silver
QUICKSHIP 7-DAY	P2: 2-circuit Powergear				
	P3: 3-circuit Powergear				
Highlighted					
option denotes					
quick ship.					

ATF7415-DTW-38: 15W, Dim-to-Warm LED Track, 2750 K, 38° BEAM ANGLE

Zor	nal Lumen S	Summary	Polar	Candela Distribution		Illuminance	at a Dist	ance
Zone 0-30 0-40 0-60 <u>60-90</u> 0-90	Lumens 877.4 962.5 1,011.0 15.0 1,026.1	% Luminaire 85.5% 93.8% 98.5% 1.5% 100%	2,600 2,167 1,733 1,300 867 433 0D: 0 433 867 433 867 1,300 1,733 2,167 2,600		2.0% 4.0% 8.0% 10.0%	Center Beam FC 637.3 fc 159.3 fc 70.8 fc 38.8 fc 26.5 fc Vert. Spread: 34.5*	1.3 2.6 3.7 6.0 6.2 Horiz: Spr	t 2.5 t t 3.7 t t 5.0 t t 6.2 t


FINISH



CRI

80






ATF7425-3038-WH: LED TRACK HEAD, 25W, 3000 K, 38° BEAM SPREAD

Zor	al Lumen S	Summary	Polar	Candela Distributio
Zone 0-30 0-40 0-60 60-90 70-100 <u>90-120</u> 0-90 90-180 0-180	Lumens 1,844.4 2,162.7 2,408.9 90.6 33.1 0.9 2,499.4 8.0 2,507.4	% Luminaire 73.6% 86.3% 96.1% 1.3% 0% 99.7% 0.3% 100%	4,300 3,583 2,887 2,150 1,433 717 CD. 0 717 717 1,433 2,150 2,887 3,583 4,300 • - 0' H	

_	Center Beam FC	Beam	Width
L	959.2 fc	1,51	1,51
	239.8 fc	2.9ft	2.9ft
L	106.6 fc	4,48	4,49
L	59.9 fc	5.9ft	5.91
	38.4 fc	7.3ft	7.38

ATF75 SERIES

Designed for residential, gallery task and accent lighting, the ATF75 series is available in 8.5W with up to 680 delivered lumens and 45W with up to 2250 delivered lumens. Dim-to-Warm color temperature capabilities are available on select models.



ATF7545



Connector Type	Color Temp.	Beam Spread	Finis
- AT	F7545 -		-
Blank : A-Line	30:3000 K	15:15°	WH : White
LL : Liteline	35:3500 K	38:38°	BK : Black
H:H-Style			SL : Silver









ATF7509-	•3038: 8.5W,	LED TRACK, 300	00 K, 38° B	EAM ANGLE	
Zona	al Lumen Su	Immary	Polar (Candela Distribution	Illun
Zone 0-30 0-40 0-60 60-90 70-100 90-120 0-90 90-180 0-180	Lumens 522.9 602.0 654.7 17.5 6.8 0.2 672.2 1.2 673.4	% Luminaire 77.6% 89.4% 97.2% 2.6% 1% 0% 99.8% 0.2% 100%	1,500 1,250 1,000 750 500 250 CD: 0 250 500 750	160' 170' 160' 150' 140' 150' 150' 100' 100' 100' 100' 100' 10	1.7ft 3.3ft 5.0ft 6.7ft 8.3ft 10.0ft
0 100	070.4	10070	1,000 1,250 1,500	VA: 0° 10° 20° 30° 40°	






22



ATF7545 -3038: 45W, LED TRACK, 3000 K, 38° BEAM ANGLE

Zone	Lumens	% Luminaire
0-30	3,280.8	73.9%
0-40	3,832.4	86.3%
0-60	4,269.8	96.1%
60-90	161.7	3.6%
70-100	60.7	1.4%
90-120	4.3	0.1%
0-90	4,431.5	99.8%
90-180	9.9	0.2%
0-180	4,441,4	100%



	Illuminance a	at a Distance
	Center Beam FC	Beam Width
8.3ft	110 fc	6.1 ft 6.1 ft
16.7ft	27,2 fc	12,3 ft 12,3 ft
25.0ft	12.1 fc	18.4 ft 18.4 ft
33.3ft	6.85 fc	24.5 ft 24.5 ft
41.7ft	4.37 fc	30.7 ft 30.7 ft
50.0ft	3.04 fc	36.8 ft 36.8 ft
	Vert. Spread: 40.4	* 📕 Horiz, Spread: 40.4*






FOCUS **SERIES**

The Focus Series is the perfect solution for galleries and other spaces where displays are regularly updated. An integrated dial allows users to select specific beam angles and change them by simply twisting the front dial of the fixture. Focus also includes a wide range of outputs from 500 - 3000 delivered lumens.




ATF8010




ATF8010 Blank : A-Line LL : Liteline H:H-Style P: 2- Cricuit Powergear Highlighted option denotes quick ship, WH : White BK : Black SL : Silver 27:2700 K 35:3500 K 90:90CRI

ATF8020






Zone	Lumens	% Luminaire
0-30	513.2	84.8%
0-40	571.9	94.5%
0-60	597.3	98.7%
60-90	7.7	1.3%
70-100	3.6	0.6%
90-120	0	0%
0-90	605.0	100%
90-180	0	0%
0-180	605.0	100%



_	Center Beam FC	Beam	Width
on _	122 fc	1.90	1,91
ıft	30.4 fc	3.88	3.8ft
in –	13.5 fc	5.70	5.61
n 🗆	7.60 fc	7.58	7.5ft
n –	4.86 fc	9.4ft	9.4ft
ın L	3.38 fc	11.3ft	11.3f


FINISH






ATF8020 -27-90: LED TRACK HEAD, 20W, 2700 K, 90 CRI, 32° BEAM SPREAD


Zonal Lumen Summary				
Zone)-30	Lumens 1,243.8	% Luminaire 78.8%		
)-40)-60	1,454.9 1.560.2	92.2% 98.8%		
60-90	18.3	1.2%		
-90	1,578.5	100%		




	Illuminance a	nt a Distar	ice
	Center Beam FC	Beam	Width
4.0ft	227 fc	2.4ft	2.3ft
8.0ft	56.9 fc	4,7ft	4.6ft
12.0ft	25.3 fc	7.18	6.9ft
16 Oft	14.2 fc	9.51	9.3ft
20.08	9.10 fc	11.88	11.6ft
24.0ft	6.32 fc	14.21	13.9ft
	rt. Spread: 32.9° 📕 Hori:	. Spread: 32.3°	




ATF8040














WALL WASH

Perfect for your commercial, institutional or high education applications, wall wash and flood lights provide a layered light look to your space. Powerful outputs range from 2400 - 4800 delivered lumens.



ATF7266-30





CRI

80

FINISH





Ordering	Guide			AIF/200 -30	: WALL V		
ordening	g duide			Zonal Lumen			
QUICKSHIP CEDAY Highlighted quick ship.	Connector Type Blank : A-Line H : H-Style L : L-Style P2 : 2-circuit Powergear P3 : 3-circuit Powergear	ATF7266-30	Finish	Zone Lume 0-30 1,599 0-40 2,46 0-60 3,677 60-90 530 70-100 214 <u>90-120 19</u> <u>0-90 4,205</u> <u>90-180 5.0</u> 0-180 4,213	1 37.99 1 58.39 0 87.19 4 12.69 8 5.1% 0% .4 99.79 0.1%		

ATF7233-30



Ordering Guide

Highlighted option denot quick ship.

Connector Type

H: H-Style L: L-Style P2: 2-circuit Powergear P3: 3-circuit Powergear

Blank : A-Line





DELIVERED



Finish


WH : White BK : Black


ATF7233-30




Zone 0-30 0-40 0-60 60-90 70-100 <u>90-120</u> 0-90 <u>90-180</u>











📕 - Max Cd: 20" H









	Illuminance	at a Distan	се
[Center Beam FC	Beam	Width
2.0ft	538.68 fc	3.0ft	4.2ft
4 Oft	134.67 fc	6.0ft	8,3ft
6.0ft	59.85 fc	9.10	12.5ft
8.00	33.67 fc	12.1ft	16.6ft
10.0ft	21.55 fc	15.1ft	20.8ft
12.0ft	14.96 fc	18.1ft	24,9ft
1	Vert. Spread: 74.1*	Horiz. Spread: 9	92.2*

TRACK HEADS & ADAPTERS

	Product Number	Finish	сст	Delivered Lumens	CRI	Wattage	Beam Spread	Accessories	Page Number
	ATF7134	Black, White	30 K	Up to 2295 lm	80+, 90	34W	19, 23, 38		-
	ATF7233-30	Black, White	30 K	Up to 2400 lm	80	30W		Louver	28
	ATF7266-30	Black, White	30 K	Up to 4800 lm	80+	60W		Louver	29
	ATF7415	Black, White	30 K, 35 K, 40 K, Dim-to-Warm	Up to 1400 lm	80+, 90	15W	15, 20, 38, 60	Snoot, Honeycomb Louver	20
	ATF7425	Black, White, Silver	30 K, 35 K, 40 K	Up to 2375 Im	80+	25W	15, 25, 38	Snoot, Honeycomb Louver	21
IRES	ATF7509	Black, White, Silver	30 K, 40 K, Dim-to-Warm	Up to 680 Im	80+	8.5W	15, 38, 60		22
A-LINE TRACK FIXTURES	ATF7545	Black, White	30 K, 35 K	Up to 4428 lm	80+	45W	15, 38		23
NE TRAC	Flight Series™ ATF7610	Black, White, Silver	30 K, Dim-to-Warm	Up to 640 Im	90	10W	6, 25, 40, 60		14
A-LI	ATF7630	Black, White, Silver	30 K, 35 K	Up to 2200 lm	90	30W	20, 29, 35		19
	FOCUS Series™ AFT8010/20/30/40	Black, White, Silver	27 K, 35 K	Up to 3000 lm	90	10W/ 20W/ 30W/ 40W	18-50° adjustable dial		24
	TEARDROP Series™ ATF8514/22/36	Black, White, Silver	27 K, 30 K, 35 K, 40 K, 50 K	Up to 3180lm	90+	14W/ 22W/ 36W	15, 25, 40, 60	Barn Door, Honeycomb Louver, Snoot, Oval Snoot	16
	Dines Series LED SP-DNG	Black, White	Dim-to-Warm, 30 K	Up to 900 Im	90+	16W	25, 35, 40	1", 2", & 4" Snoot	10
	Flex Series 15/22/38	Black, White, Silver	27 K, 30 K, 35 K, 40 K	Up to 4200 lm	90+	15W/ 22W/ 38W	15, 25, 40, 60	Barn Door, Honeycomb Louver, Snoot, Oval Snoot, Extender, Linear Spread Lens, Softening Lens	6
URES	APOLLO AO1008	Black, White, Silver	27 K, 30 K	Up to 605 Im	90	8W	38		12
CK FIXT	DELTA DA2010	Black, White, Silver	27 K, 30 K, 40 K	Up to 1000 lm	80+, 90	10W	38		13
LITELINE TRACK FIXTURES	SORA SO1008	Black, White, Silver	27 K, 30 K	Up to 611 Im	90	8W	38		13
LITEL	VEGA VA6510	Black, White, Brushed Nickel	30 K	Up to 680 Im	80+	10W	25		-

CUSTOMIZE CONNECTOR STYLES



TRACK





Ordering

TK60

06 : 6'

08:8'

12:12'1


WHITE (WH) BLACK (BK) SILVER (SL) BRUSHED

NICKLE (BN)

Guide	
Length	Finish
02 : 2'	WH : White
04 : 4'	BK : Black

SL : Silver

BN : Brushed Nickel



Field Cuttable

2' 🛏

6'

8'

12' H

FINISH

Notes: ¹2 Circuit track not available in 12'. ² Silver finish only available with 2 Circuit track. ³ Brushed Nickel finish only available with 1 Circuit track.






A-LINE

. /	Commercial	

Single / 2 Circuit 120V










POWERGEAR

- 2 Circuit / 2 Neutral
- 3 Circuit / 1 Neutral


TRACK LENGTHS



FINISH







POWERGEARTRACK.COM

INFO@POWERGEARTRACK.COM

ADD RIGIDITY

Provide strength to track with A-Beam and H-Channel. Ideal for commercial applications including retail and hospitality, these rigid lighting channels require fewer suspension points allowing for a cleaner ceiling space.




COMMERCIAL

Single / 2 Circuit 120V

FEATURES


• Ability to add up-lighting for design flexibility

TRACK LENGTHS



FINISH









FEATURES

• 12 ft spacing between suspension points

Integrate track into store fixtures in retail environment

TRACK LENGTHS

WHITE (WH) BLACK (BK)








3-5/64"

78mm

MUTUL

1-49/64" 45mm



PRECISIONPRO **TRIMLESS MADE EASY**

A-Line and Powergear track can be trimless with the use of PrecisionPro pre-formed recessed drywall channel. PrecisionPro installs like any other drywall and then the track simply surface mounts into the channel and corner pieces, avoiding the headaches of traditional recessed track systems. PrecisionPro comes standard with a wood backing, or upgrade to a steel backing for added support. Upon order 2 pieces are packed together to ensure the drywall ships safely to the job site.

- ✓ Reduce intensive labor & costs
- ✓ Sleek finish with minimal effort
- ✓ Level 5 finish

2' H 4' H

LENGTHS

THICKNESS

1/2" _____ 5/8"

Double 5/8" Fire Rated



Install Recessed Track Kit into building's frame





3. Install track as surface mount





A-Line's **Precision**Pro drywall program is the only solution to have trimless. fire-rated track!

TRACK SYSTEMS

TRACK SYSTEM DIAGRAM

GUIDE

A-line 1-Circuit Overgear 2-Circuit / 2 Neutral

A-line 2-Circuit

Powergear 3-Circuit / 1 Neutral

		Description	Liteline	A-Line	Powergear
А	ie a	Live-end Connector	LE6110	ATKP09 ATKP09-2C	PRO-2431 (L/R)* PRO-0431 (L/R)*
	100	Live End Conduit Feed	CA6106	ATKP06 ATKP06-2C	
В		"T" Connector	TC6103	ATKP03 ATKC03-2C	PRO-2436(L/R)(1/2)* PRO-0436(L/R)(1/2)*
С		Middle Connector	IC6101	ATKC01 ATKC01-2C	PRO-2433 PRO-0433 PRO-0433(A)* PRO-0433(A)*
D		"L" Connector	LC6102	ATKP02 ATKC02-2C	PRO-2435(L/R)* PRO-0435(L/R)* PRO-M435 PRO-M435
E		Flexible "L " Connector	FC6105	ATKC05	PRO-2439 PRO-0439
F	22	"X" Connector	XC6104	ATKP04-2C	PRO-2437 PRO-0437
Н	A.	End Cap	TK6000-END	ATK0-ENDCAP-1C ATK0-ENDCAP-2C	PRO-2432 PRO-0432
I		Center Feed	FC6108	ATKP08 ATKP02 ATKC02-2C	PRO-2434 PRO-0434
	and the second s	Wired End	WE6110	ATKP10	
	- des	Live End With Canopy	LE611	ATKP11 ATKP11-2C	
		Live End With Canopy For T-Bar		ATKP12-2C	
		Monopoint		ATKP109	
	T I	Hollow Stem Suspension Rod	LL-ATKXW	ATKXW	
		Stem Rod Kit With Hollow Rod	TDR62	A-TDR62	
		Track Hook / Track Receptacle		ATKA320/ ATKA321	



A-LINE CURRENT LIMITERS



ATKPCL-06-1C Single circuit live end narrow current limiter




ATKPCL-09-1C ATKPCL-09-2C Single/two circuit dual live end canopy with current limiter



ATKPCL-11-1C ATKPCL-11-2C Single/two circuit live end canopy current limiter



ATKP11T-2C Two circuit live end power feed with canopy cover for t-bar



NOTEO	
NOTES:	

Liteline Corporation Copyright © 2020 All rights reserved. Telephone 416.996.1856 1.866.730.7704 Fax 905.709.5255 1.888.738.9736



