



**STANDARD** offers a full line of premium quality, professional grade reflector halogen lamps.



| Order code   | Description                   | Watts (W) | Base | Volts (V) | Colour temp. (K) | Beam angle (°) | Beam spread  | CBCP (cd) | Average life (hrs) | Initial lumens (lm) | Case qty |
|--|-------------------------------|-----------|------|-----------|------------------|----------------|--------------|-----------|--------------------|---------------------|----------|
| <b>PAR16</b>   |                               |           |      |           |                  |                |              |           |                    |                     |          |
| MOL : 3 7/32 in. (82 mm)      Dia. : 2 in. (51 mm)       |                               |           |      |           |                  |                |              |           |                    |                     |          |
| 50974  | H40PAR16/NFL/2.5M/130V/STD    | 40        | E26  | 130       | 2 800            | 30             | Narrow Flood | 530       | 2 500              | 400                 | 120      |
| 50975  | H60PAR16/NFL/2.5M/130V/STD    | 60        | E26  | 130       | 2 800            | 30             | Narrow Flood | 1 100     | 2 500              | 650                 | 120      |
| <b>PAR20</b>   |                               |           |      |           |                  |                |              |           |                    |                     |          |
| MOL : 3 7/32 in. (82 mm)      Dia. : 2.5 in. (63.5 mm)   |                               |           |      |           |                  |                |              |           |                    |                     |          |
| 51084  | H35PAR20/NFL/2.5M/120V/STD    | 35        | E26  | 120       | 2 800            | 30             | Narrow Flood | 630       | 2 500              | 315                 | 15       |
| 51083  | H35PAR20/NFL/5M/130V/STD      | 35        | E26  | 130       | 2 800            | 28             | Narrow Flood | 630       | 5 000              | 235                 | 15       |
| <sup>1</sup> 50738                                       | H50PAR20/NFL/2.5M/120V/STD    | 50        | E26  | 120       | 2 800            | 28             | Narrow Flood | 1 050     | 2 500              | 550                 | 15       |
| <sup>1</sup> 51146                                       | H50PAR20/NFL/5M/130V/STD      | 50        | E26  | 130       | 2 800            | 28             | Narrow Flood | 1 050     | 5 000              | 410                 | 15       |
| <b>PAR30</b>   |                               |           |      |           |                  |                |              |           |                    |                     |          |
| MOL : 3 23/32 in. (93 mm)      Dia. : 3 3/4 in. (95 mm)  |                               |           |      |           |                  |                |              |           |                    |                     |          |
| <sup>1</sup> 10382                                       | H50PAR30/NSP/5M/130V/STD      | 50        | E26  | 130       | 2 800            | 13             | Narrow Spot  | 5 000     | 5 000              | 495                 | 15       |
| <sup>1</sup> 10383                                       | H50PAR30/NFL/5M/130V/STD      | 50        | E26  | 130       | 2 800            | 30             | Narrow Flood | 2 000     | 5 000              | 495                 | 15       |
| <sup>1</sup> 10381                                       | H50PAR30/FL/2.5M/120V/STD     | 50        | E26  | 120       | 2 800            | 40             | Flood        | 1 350     | 2 500              | 660                 | 15       |
| <sup>1</sup> 50739                                       | H50PAR30/FL/5M/130V/STD       | 50        | E26  | 130       | 2 800            | 40             | Flood        | 1 350     | 5 000              | 495                 | 15       |
| <sup>1</sup> 50016                                       | H75PAR30/NSP/2.5M/120V/STD    | 75        | E26  | 120       | 2 800            | 10             | Narrow Spot  | 8 000     | 2 500              | 1 100               | 90       |
| <sup>1</sup> 10387                                       | H75PAR30/NSP/5M/130V/STD      | 75        | E26  | 130       | 2 800            | 13             | Narrow Spot  | 8 000     | 5 000              | 825                 | 15       |
| <sup>1</sup> 10385                                       | H75PAR30/FL/2.5M/120V/STD     | 75        | E26  | 120       | 2 800            | 40             | Flood        | 2 000     | 2 500              | 1 100               | 15       |
| <sup>1</sup> 50740                                       | H75PAR30/FL/5M/130V/STD       | 75        | E26  | 130       | 2 800            | 40             | Flood        | 2 000     | 5 000              | 825                 | 15       |
| <b>PAR30LN</b>   |                               |           |      |           |                  |                |              |           |                    |                     |          |
| MOL : 4 13/16 in. (122 mm)      Dia. : 3 3/4 in. (95 mm) |                               |           |      |           |                  |                |              |           |                    |                     |          |
| <sup>1</sup> 50229                                       | H50PAR30/LN/NSP/2.5M/120V/STD | 50        | E26  | 120       | 2 800            | 9              | Narrow Spot  | 5 000     | 2 500              | 660                 | 90       |
| <sup>1</sup> 50084                                       | H50PAR30/LN/NFL/5M/130V/STD   | 50        | E26  | 130       | 2 800            | 25             | Narrow Flood | 2 000     | 5 000              | 495                 | 15       |
| <sup>1</sup> 10384                                       | H50PAR30/LN/FL/2.5M/120V/STD  | 50        | E26  | 120       | 2 800            | 40             | Flood        | 1 350     | 2 500              | 660                 | 15       |
| <sup>1</sup> 50741                                       | H50PAR30/LN/FL/5M/130V/STD    | 50        | E26  | 130       | 2 800            | 40             | Flood        | 1 350     | 5 000              | 495                 | 15       |
| <sup>1</sup> 50052                                       | H75PAR30/LN/NSP/2.5M/120V/STD | 75        | E26  | 120       | 2 800            | 9              | Narrow Spot  | 8 000     | 2 500              | 1 100               | 15       |
| <sup>1</sup> 50051                                       | H75PAR30/LN/NFL/2.5M/120V/STD | 75        | E26  | 120       | 2 800            | 25             | Narrow Flood | 2 400     | 2 500              | 1 100               | 90       |
| <sup>1</sup> 10388                                       | H75PAR30/LN/FL/2.5M/120V/STD  | 75        | E26  | 120       | 2 800            | 40             | Flood        | 2 000     | 2 500              | 1 100               | 15       |
| <sup>1</sup> 50742                                       | H75PAR30/LN/FL/5M/130V/STD    | 75        | E26  | 130       | 2 800            | 40             | Flood        | 2 000     | 5 000              | 825                 | 15       |



<sup>1</sup>This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.

# Reflector Lamps