

Project:		Type:
Drawn by:	Catalogue #:	Date:





LED TAPE KIT LOW VOLTAGE LED TAPE KIT

Stanpro's LED Tape kits are designed to add ambiance and character to any setting. Delivering even, brilliant light, the color changing RGB, cool white and warm white colors can be used in a multitude of applications, both indoor and outdoor, ranging from under cabinets to cove and perimeter applications.

FEATURES AND SPECIFICATIONS

Construction

Technical specifications

- Available light outputs: 1.6W/ft and 1.7W/ft
- Available in RGB, warm white and cool white
- Estimated lifespan of 50 000 hours to L70
- Included in the box :
 - 1 Tape light 16.4' (5m)
 - 1 plug-in driver
 - 1 RGB remote control (for RGB kit only)

Installation

- 16.4' length
- Variety of fixing accessories : RGB connector, connector and mounting clips
- No need for soldering with connectors and accessories available
- Direct line voltage 120V no driver required
- Additional driver can be ordered seperately
- Can be installed outside
- Cannot be directly exposed to water or weather

Compliances

- cULus
- IP64 rating

warranty





OVERVIEW

Light source	LED
Watts per foot (W/ft)	5.6
Lumen output per foot (Im/ft)	2 620 - 11 880
Efficiency (Im/W)	145
Color temperature (K)	RGB, warm white, cool white
CRI	90+



QUICK SHIP AND TECHNICAL SPECIFICATION TABLE : 1

Order code	Description	Watts (oer reel V)	Volts	Color	Len	gth	Life L70		n output m)		ber of chips	Dimming capability	Case qty
		(per ft.)	(per m)	(VDC)		(ft.)	(m)	(hrs)	(per ft.)	(per m)	(per ft.)	(per m)	(Yes/No)	(master)
LED T	Tape Kits													
61953	LED/TAPE/16.4'/5050/RGB KIT/12V/50M/STD	1.6	5.4	12	RGB	16.4	5	50 000	-	-	9	30	Yes	20
61954	LED/TAPE/16.4'/5050/WW KIT/12V/50M/STD	1.7	5.6	12	Warm white	16.4	5	50 000	145	175.6	9	30	No	20
61955	LED/TAPE/16.4'/5050/CW KIT/12V/50M/STD	1.7	5.6	12	Cool white	16.4	5	50 000	145	175.6	9	30	No	20
Plug-	-in Drivers - Non-dimmable													
62265	LED/TAPE/36W/12V/WW+CW/PS/ND/STD	-	-	12	White	6.56	2	-	-	-	-	-	-	50
62266	LED/TAPE/36W/12V/RGB/PS/ND/STD	-	-	12	White	6.56	2	-	-	-	-	-	-	50

¹ QUICK SHIP: Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

INCLUDED IN THE BOX

- 1 tape light 16.4' (5 m)
- 1 plug-in driver
- 1 RGB remote control (for RGB kit only)







ACCESSORIES

Order code	Description	Туре	Case qty (inner/master)		
61956	LED/TAPE/RGB/CONNECTOR/STD	RGB Connector	10/50		
61957	LED/TAPE/WW+CW/CONNECTOR/STD	Connector	10/100		
62017	LED/10PCS TAPE LIGHT 12V MOUNTING CLIPS	Mounting clips	1/100		



Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

