

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



Nominal length : 46 in. (1 168.4 mm) Dia. : 1 in. (26 mm)

ORDERING INFORMATION

Order code: 65049
 Description: LED/T8/15W/835/46/METRIC/STD
 UPC: 69549650497
 Case quantity: 25

PERFORMANCE DATA

Shape: T8
 Base: G13
 Starting method: Instant, Rapid & Program Start
 Lamp voltage (VAC): 120 V-277 V/347 V
 Color temperature (K)**: 3 500
 Average life (L70 hours): 50 000
 CRI: 83
 Beam angle (°): 240
 Operating temperature range: -20°C / -4°F to 45°C / 113°F

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %

Order code	Average System Watts (W)			Initial Lumens (lm)*		
	LBF	NBF	HBF	LBF	NBF	HBF
65049	16	18	26	1 650	1 850	2 650



DAMP



COMPLIANT



NO
MERCURY



WARRANTY



CAUTIONS

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.
 Direct replacement for 32 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.