

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



Nominal length : 48 in. (1 220 mm) Dia. : 1 in. (26 mm)

ORDERING INFORMATION

Order code: 65474
 Description: LED/T8/S4/13W/835/48/STD
 UPC: 69549654747
 Case quantity: 25

PERFORMANCE DATA

Shape: T8
 Base: G13
 Starting method: Instant, Rapid & Program Start
 Lamp voltage (VAC): 120 V - 277 V / 347 V
 Color temperature (K)**: 3 500
 Average life (L70 hours): 50 000
 CRI: >80
 Beam angle (°): >240
 Operating temperature range: -20°C / -4°F to 45°C / 113°F
 DLC Listed: DLC Standard

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %

Order code	Average System Watts (W)			Initial Lumens (lm)*		
	LBF	NBF	HBF	LBF	NBF	HBF
65474	14	16	22	1 550	1 800	2 400



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

CAUTIONS

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.
 Direct replacement for 25 and 28 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.