



A19



A19 GU24



A19 15 W & Trilight



A19 4 pack

Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	Finish	CRI	Life L70 (hrs)	Lumen output (lm)	Traditional equivalent (W)	Dimming capability (Yes/No)	Case qty (inner/master)
A19												
40 W equivalent												
64809	LED/OMNI/S3/5.5W/27K/STD	5.5	E26	120	2 700	Frost	81	25 000	455	40	Yes	1/60
66178	LED/A19/S4/6W/40K/STD	6	E26	120	4 000	Frost	86	25 000	535	40	Yes	6/48
64812	LED/OMNI/S3/5.5W/50K/STD	5.5	E26	120	5 000	Frost	86	25 000	545	40	Yes	1/60
67948	LED/A19/S5/6W/27K/STD	6	E26	120	2 700	Frost	80	25 000	480	40	Yes	1/100
60 W equivalent												
66180	LED/A19/S4/9.8W/27K/STD	9.8	E26	120	2 700	Frost	83	25 000	814	60	Yes	6/48
66183	LED/A19/S4/9.8W/50K/STD	9.8	E26	120	5 000	Frost	85	25 000	858	60	Yes	6/48
67953	LED/A19/S5/9W/30K/STD	9	E26	120	3 000	Frost	80	25 000	800	60	Yes	1/100
67954	LED/A19/S5/9W/40K/STD	9	E26	120	4 000	Frost	80	25 000	800	60	Yes	1/100
60 W equivalent - 4 pack												
66970	LED/A19/9.8W/27K/STD 4P	9.8	E26	120	2 700	Frost	83	25 000	814	60	Yes	6/48
66971	LED/A19/9.8W/30K/STD 4P	9.8	E26	120	3 000	Frost	83	25 000	848	60	Yes	6/48
66972	LED/A19/9.8W/40K/STD 4P	9.8	E26	120	4 000	Frost	86	25 000	874	60	Yes	6/48
66973	LED/A19/9.8W/50K/STD 4P	9.8	E26	120	5 000	Frost	85	25 000	858	60	Yes	6/48
60 W equivalent - GU24												
66275	A19/9.8W/27K/GU24/PRO/STD	9.8	GU24	120	2 700	Frost	83	25 000	814	60	Yes	6/48
66276	A19/9.8W/30K/GU24/PRO/STD	9.8	GU24	120	3 000	Frost	82	25 000	887	60	Yes	6/48
66277	A19/9.8W/40K/GU24/PRO/STD	9.8	GU24	120	4 000	Frost	86	25 000	868	60	Yes	6/48
75 W equivalent												
66184	LED/A19/S4/11W/27K/STD	11	E26	120	2 700	Frost	81	25 000	1 109	75	Yes	6/48
66186	LED/A19/S4/11W/40K/STD	11	E26	120	4 000	Frost	85	25 000	1 196	75	Yes	6/48
66187	LED/A19/S4/11W/50K/STD	11	E26	120	5 000	Frost	86	25 000	1 178	75	Yes	6/48
67957	LED/A19/S5/12W/30K/STD	12	E26	120	3 000	Frost	80	25 000	1 100	75	Yes	1/100
100 W equivalent												
66188	LED/A19/S4/15W/27K/STD	15	E26	120	2 700	Frost	82	25 000	1 629	100	Yes	6/48
66189	LED/A19/S4/15W/30K/STD	15	E26	120	3 000	Frost	81	25 000	1 630	100	Yes	6/48
66190	LED/A19/S4/15W/40K/STD	15	E26	120	4 000	Frost	85	25 000	1 692	100	Yes	6/48
66191	LED/A19/S4/15W/50K/STD	15	E26	120	5 000	Frost	85	25 000	1 725	100	Yes	6/48
A21												
40 W equivalent												
67960	LED/A21/S5/15W/27K/STD	15	E26	120	2 700	Frost	80	25 000	1 600	100	Yes	1/100
67961	LED/A21/S5/15W/30K/STD	15	E26	120	3 000	Frost	80	25 000	1 600	100	Yes	1/100
67962	LED/A21/S5/15W/40K/STD	15	E26	120	4 700	Frost	80	25 000	1 600	100	Yes	1/100
67963	LED/A21/S5/15W/50K/STD	15	E26	120	5 000	Frost	80	25 000	1 600	100	Yes	1/100
Trilight												
65613	LED/A19/S2/12W/27K/3WAY/STD	3 9 12	E26	120	2 700	Frost	81	25 000	280 950 1 200	30 70 100	No	6/24
65614	LED/A19/S2/12W/30K/3WAY/STD	3 9 12	E26	120	3 000	Frost	83	25 000	280 950 1 200	30 70 100	No	6/24

Lumen values are derived from photometric testing. For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com

