

Technical Information Bulletin


CHOICE LED Lamps



Date: _____ Name of distributor: _____
 In hands date of project: _____ Client #: _____
 Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 66271
 Description: A19/9.5W/27K/ND/CHOICE/STD 4P
 UPC: 6954966711
 Case quantity: 12 x 4 pack



PERFORMANCE DATA

Shape: A19 4 pack
 Base: E26
 Watts(W): 9.5
 Volts (VAC): 120
 Colour temperature (K)**: 2 700
 Average life (L70 hours): 15 000
 Initial lumens (lm)*: 922
 Initial lumens per watt (lm/W): 97
 CRI: 82
 Beam angle: 220
 Power factor: 0.6
 Operating temperature range: -20 °C to 45 °C (-4 °F to 113 °F)

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %



This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Suitable for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Do not use with dimmers.
- For complete warranty information visit www.standardpro.com.
- 3 Years Limited Warranty.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____ Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
 Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.