

## Weather Proof Cover - Low-Profile Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hz, White

Item WP6000W



### PRODUCT DESCRIPTION

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

### FEATURES

- ▶ 100% Paintable surface
- ▶ Complies with 2020 NEC Article 314.15 for wet locations
- ▶ UL Certified for Type 3R outdoor enclosures
- ▶ Meets requirements for cold impact testing: -60° F (-51° C)
- ▶ Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- ▶ Lockable hasp: All models accept up to 0.19" dia shank
- ▶ Impact rated: 12 lbf. impact test to ensure cover remains intact
- ▶ Warranty: 1-year limited
- ▶ NEW Faster Installation, Pre-Set for GFCI, No insert required
- ▶ Two inserts provided with all models that allow each model to meet multiple installations (up to 8 configurations)

### APPLICATIONS

- ▶ Receptacle Protection

### TECHNICAL DATA

#### General

Model Number	WP6000W
Description	Low-Profile Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hz, White
UPC Code	078275149915
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited

#### Mechanical Specifications

Number of Included Inserts	2
Hinge Direction	Vertical/Horizontal
Is Extra-Duty Rated	No

#### Dimensions

Product Dimensions (H x W x D) in	5.5 x 3.75 x 1.5 in
Expandable Depth Mm	54
Expandable Depth In	2 1/8
Accepted Cord Size Max	1x16 AWG
Box Type	Single

#### Material Specifications

Color	Clear; White
Weatherproof Cover Material	UV Stabilized Plastic

### Packaging

Shipping Weight (lbs)	0.35
Unit Carton Dimensions (H x W x L) in	1.5 x 3.7 x 5.5 in

### Standards and Certifications

UL Certification	cULus
CSA Certification	cCSAus
RoHS Certification	Yes