

Weather Proof Cover - Low-Profile Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hz, Bronze

Item WP6000BR



PRODUCT DESCRIPTION

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

FEATURES

- ▶ 100% Paintable surface
- ▶ Complies with 2020 NEC Article 314.15 for wet locations
- ▶ UL Certified for Type 3R outdoor enclosures
- ▶ Meets requirements for cold impact testing: -60° F (-51° C)
- ▶ Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- ▶ Lockable hasp: All models accept up to 0.19" dia shank
- ▶ Impact rated: 12 lbf. impact test to ensure cover remains intact
- ▶ Warranty: 1-year limited
- ▶ NEW Faster Installation, Pre-Set for GFCI, No insert required
- ▶ Two inserts provided with all models that allow each model to meet multiple installations (up to 8 configurations)

APPLICATIONS

- ▶ Receptacle Protection

TECHNICAL DATA

General

| | |
|--------------------------------|--|
| Model Number | WP6000BR |
| Description | Low-Profile Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hz, Bronze |
| UPC Code | 078275149922 |
| Brand | Intermatic |
| Country of Origin (Intermatic) | MEXICO |
| Warranty Period | 1-Year limited |

Mechanical Specifications

| | |
|----------------------------|---------------------|
| Number of Included Inserts | 2 |
| Hinge Direction | Vertical/Horizontal |
| Is Extra-Duty Rated | No |

Dimensions

| | |
|-----------------------------------|---------------------|
| Product Dimensions (H x W x D) in | 5.5 x 3.75 x 1.5 in |
| Expandable Depth Mm | 54 |
| Expandable Depth In | 2 1/8 |
| Accepted Cord Size Max | 1x16 AWG |
| Box Type | Single |

Material Specifications

| | |
|-----------------------------|-----------------------|
| Color | Clear; Bronze |
| Weatherproof Cover Material | UV Stabilized Plastic |

Packaging

| | |
|---------------------------------------|--------------------|
| Shipping Weight (lbs) | 0.35 |
| Unit Carton Dimensions (H x W x L) in | 1.5 x 3.7 x 5.5 in |

Standards and Certifications

| | |
|--------------------|--------|
| UL Certification | cULus |
| CSA Certification | cCSAus |
| RoHS Certification | Yes |