

# Weather Proof Cover - Low-Profile Extra-Duty Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hrz, Bronze

### Item WP7000BR



LU us S

#### PRODUCT DESCRIPTION

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

# **FEATURES**

- ► 100% Paintable surface
- ► Complies with 2020 NEC Article 406.9 (B)(1) for wet locations and extra-duty applications
- ► CEC Article 26-702 Compliant
- ► UL Certified for Type 3R outdoor enclosures
- ► Meets requirements for cold impact testing: -60° F (-51° C)
- ► Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- ► Lockable hasp: All models accept up to 0.19" dia shank
- ▶ Impact rated: 12 lbf. impact test to ensure cover remains intact
- ► Reinforced hinge pin designed to exceed 40 lbf. hinge hang/stress test
- ► Warranty: 1-year limited
- ▶ NEW Faster Installation, Pre-Set for GFCI, No insert required
- Two inserts provided with all models that allow each model to meet multiple installations (up to 8 configurations)

### **APPLICATIONS**

► Receptacle Protection

# **TECHNICAL DATA**

General	
Model Number	WP7000BR
Description	Low-Profile Extra-Duty Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hrz, Bronze
UPC Code	078275149892
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited

Mechanical Specifications		
Number of Included Inserts	2	
Hinge Direction	Vertical/Horizontal	
Is Extra-Duty Rated	Yes	

Dimensions	
Product Dimensions (H x W x D) in	5.5 x 3.75 x 1.5 in
Expandable Depth Mm	54
Expandable Depth In	2 1/8
Accepted Cord Size Max	1x16 AWG
Box Type	Single

# **Material Specifications**

Color Clear; Bronze



Weatherproof Cover Material	UV Stabilized Plastic	
Packaging		
Shipping Weight (lbs)	0.35	
Unit Carton Dimensions (H x W x L) in	1.5 x 3.7 x 5.5 in	
Standards and Certifications		
UL Certification	cULus	
CSA Certification	cCSAus	
RoHS Certification	Yes	