

Weather Proof Cover - Low-Profile Plastic In-Use Weatherproof Cover, Double-Gang, Vrt, Gray

Item WP6200G



PRODUCT DESCRIPTION

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

FEATURES

- ► 100% Paintable surface
- ► Complies with 2020 NEC Article 314.15 for wet locations
- ► UL Certified for Type 3R outdoor enclosures
- ► Meets requirements for cold impact testing: -60° F (-51° C)
- ► Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- ► Lockable hasp: All models accept up to 0.19" dia shank
- ► Impact rated: 12 lbf. impact test to ensure cover remains intact
- ► Warranty: 1-year limited
- ▶ NEW Faster Installation, Pre-Set for GFCI, No insert required
- ► Four inserts provided with all models that allow each model to meet multiple installations (up to 16 configurations)

APPLICATIONS

► Receptacle Protection

TECHNICAL DATA

| General | |
|--------------------------------|---|
| Model Number | WP6200G |
| Description | Low-Profile Plastic In-Use Weatherproof Cover, Double-Gang, Vrt, Gray |
| UPC Code | 078275149960 |
| Brand | Intermatic |
| Country of Origin (Intermatic) | MEXICO |
| Warranty Period | 1-Year limited |

| Mechanical Specifications | | |
|----------------------------|----------|--|
| Number of Included Inserts | 4 | |
| Hinge Direction | Vertical | |
| Is Extra-Duty Rated | No | |

| Dimensions | |
|-----------------------------------|----------------------|
| Product Dimensions (H x W x D) in | 5.5 x 5.609 x 1.5 in |
| Expandable Depth Mm | 54 |
| Expandable Depth In | 2 1/8 |
| Accepted Cord Size Max | 1x16 AWG |
| Box Type | Double |

| Material Specifications | |
|-----------------------------|-----------------------|
| Color | Clear; Gray |
| Weatherproof Cover Material | UV Stabilized Plastic |



| Packaging | |
|---------------------------------------|----------------------|
| Shipping Weight (lbs) | 0.5 |
| Unit Carton Dimensions (H x W x L) in | 5.45 x 5.6 x 1.45 in |

| Standards and Certifications | | |
|------------------------------|--------|--|
| UL Certification | cULus | |
| CSA Certification | cCSAus | |
| RoHS Certification | Yes | |