

Project Name

Location

Prepared By



## SATCO S49397

120W/LED/HP/850/100-277V/EX39

### Notes

[www] 01-24-2020 02:50:01

### General

Status	Active
Watts	120W
HID Equivalent	600W
Volts	100V-277V
Shape	Corncob
Base	Extended Mogul
ANSI Base	EX39
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	16560L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	35000
Lamp Type	LED HID
Technology	LED
Min Compartment Size	Length: 9.25 in. Width: 9.25 in. Height: 17.32 in.
Ballasting Requirements	Ballast Bypass

### Electrical

Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Base Up or Base Down Only
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +65C (+149F)

### Physical

MOL	10.26
MOD	4.72
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	White
Photocell	No
Weight (lb.)	3.75

### Additional Information

Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus Classified; cULus Listed
Location Rating	Damp
Energy Star	No
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

