

# Pivot

When searching for lighting flexibility, look no further than our 3", 4" & 6" flat gimbal LED downlights. With powerful lumen output and the ability to direct light with a 360° rotation and a 90° tilt angle, this product will meet your every need.

**UPGRADE**

WET

90°  
SWIVEL/DIRECTIONAL

ETL US  
Intertek

IC  
RATED

AIR TIGHT

COLOR TEMPERATURE\*

2700k 3000k 3500k 4000k 5000k



\*Models FGM3-CC , FGM4-CC and FGM6-CC only

| Model          | Size | Watts  | Delivered lumens | LED lumens | CRI | Color °T                             | Voltage |
|----------------|------|--------|------------------|------------|-----|--------------------------------------|---------|
| <b>FGM4-3K</b> | 4"   | 9 W    | 700 lm           | 850 lm     | 90  | 3000 K                               | 120 V   |
| <b>FGM3-CC</b> | 3"   | 6 W    | 540 lm           | 690 lm     | 90  | 2700, 3000,<br>3500, 4000,<br>5000 K | 120 V   |
| <b>FGM4-CC</b> | 4"   | 9 W    | 700 lm           | 850 lm     |     |                                      |         |
| <b>FGM6-CC</b> | 6"   | 14.5 W | 1050 lm          | 1200 lm    |     |                                      |         |

### Specifications

Every fixture includes a junction box with integrated dimmable driver  
 Can be daisy chained  
 Superior LED performance and lifespan  
 90° tilting, 360° rotation  
 Minimal heat emission  
 Aluminum construction  
 Switch-selectable CCT: 2700K/3000 K/3500 K/4000 K/5000 K\*  
 Low profile  
 40° beam spread  
 IC certification (suitable for direct contact with insulation)  
 Air-tight certified as per ASTM E283-04  
 Suitable for wet locations  
 Refer to website for dimmer compatibility  
 Ideal operating temperature:  
 -20° to 40° C  
 5-year warranty

### Finish

- **BK** Black
- **SN** Satin Nickel (FGM4, FGM6 only)
- **WH** White

### Accessories

- RFP-UNI**  
Universal rough-in plate
- RFP-46**  
Rough-in plate for 4" and 6" models

### Order example

**FGM4-CC-BK**  
 4" flat gimbal recessed downlight with 700 Lumens at 3000 K in a black finish

### Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALI representative for more information.

