




Long-term durability for hard use applications.


5262, 5362

Corrosion-resistant plated steel straps and high-strength nylon faces make these receptacles perfect for any hard use application. They feature one-piece, triple-wipe brass contacts for lasting retention. And screw-pressure-plate back wiring makes installation fast and easy.

Features & Benefits



3rd Party Compliance

 UL Listed, File Number E140596, Standard UL498. Federal Specification WC596.
CSA Certified File Number LR16063, Standard CSA-C22.2 No. 42 General Use Receptacles.
Conforms to NEMA WD-1 and WD-6.

Technical Information

Performance

Electrical

Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical


Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device

Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

Materials

Face	Nylon
Back Body	PVC
Line Contacts	.032 688 Brass
Mounting Strap	.042" Plated Steel
Ground Contacts	.040 688 Brass
Pressure Plate	.080 Steel
Terminal Screws	#8 Tri-Drive Brass (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Brass
Assembly Drive Screw	Zinc-Plated Steel
Auto-Ground Clip	Stainless Steel
Mounting Screws	Tri-Drive Steel



**Dimensions for
15 & 20 Amp**

Warranty

One year

Ordering Information

Duplex Receptacles Back & Side Wire

Catalog Number	Rating		Color	NEMA Config. No.
	A	VAC		
5262I	15	125	Ivory	5-15R
5262W	15	125	White	5-15R
5262	15	125	Brown	5-15R
5262GRY	15	125	Gray	5-15R
5262BK	15	125	Black	5-15R
5262RED	15	125	Red	5-15R
5262LA	15	125	Light Almond	5-15R
5262BL	15	125	Blue	5-15R
5362I	20	125	Ivory	5-20R
5362W	20	125	White	5-20R
5362	20	125	Brown	5-20R
5362GRY	20	125	Gray	5-20R
5362BK	20	125	Black	5-20R
5362RED	20	125	Red	5-20R
5362LA	20	125	Light Almond	5-20R
5362BL	20	125	Blue	5-20R
5362YLW	20	125	Yellow	5-20R
5362OR	20	125	Orange	5-20R



NEMA
5-15R




NEMA
5-20R

Vertical Markets

- Health Care
- Education
- Institutional

Also available in the radiant® collection

- PlugTail®
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- USB Charging Devices
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- Plug Load Control Solutions
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

