


## PASS & SEYMOUR® **Specification & Hospital Grade** USB Chargers 15 & 20A, 125V



## Charge ahead with Specification and Hospital Grade USB Type-C receptacles.

TR15USBAC, TR15USBCC, TR20USBAC, TR20USBCC TR15HUSBAC, TR15HUSBCC, TR20HUSBAC, TR20HUSBCC

Pass & Seymour<sup>®</sup> Tamper-Resistant Duplex Receptacles with USB Charging capabilities are designed with strength and durability in mind. They were designed for the commercial market, and are capable of withstanding heavy use due to their UL Fed Spec certification. This product features an an improved overall 3.1A USB charging output with current sharing technology, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The posted terminal screws and external pressure plates allow for faster, easier, and more reliable back & side-wire terminations.



#### **3rd Party Compliance**

Features & Benefits




cULus Listed, UL Listed Complies with test requirements UL 498, UL 1310, Federal Specification WC-596, CSA C22.2 No. 42, CSA C22.2 No. 223



**Ordering Information** 

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Maximum Temperature Rise	30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current
No-load power draw	48.2 mW
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire
Product Identification	Ratings are a permanent part of device
Environmental	
Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact
RoHS	Compliant



Dimensional information is the same for all models.

#### Materials

Face	Polycarbonate
Body	Nylon
Contacts	CDA 260 Brass
Mounting Strap	.049" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate For Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel
Auto-Ground Clip	Stainless Steel

Warranty

1 Year

# **L**legrand<sup>®</sup>

**PASS & SEYMOUR®** Specification & Hospital Grade USB Chargers 15 & 20A, 125V

#### **Ordering Information**

## Specification Grade USB Type-A/Type-C Chargers with Duplex Tamper-Resistant Receptacles


Catalog Number	Description	Ratir A	ng V	Color	NEMA Config. No.
TR15USBAC	Spec Grd - A/C	15	125	Brown	5-15R
TR15USBACBK	Spec Grd - A/C	15	125	Black	5-15R
TR15USBACGRY	Spec Grd - A/C	15	125	Grey	5-15R
TR15USBACI	Spec Grd - A/C	15	125	lvory	5-15R
TR15USBACLA	Spec Grd - A/C	15	125	Light Almond	5-15R
TR15USBACW	Spec Grd - A/C	15	125	White	5-15R
TR20USBAC	Spec Grd - A/C	20	125	Brown	5-20R
TR20USBACBK	Spec Grd - A/C	20	125	Black	5-20R
TR20USBACGRY	Spec Grd - A/C	20	125	Grey	5-20R
TR20USBACI	Spec Grd - A/C	20	125	lvory	5-20R
TR20USBACLA	Spec Grd - A/C	20	125	Light Almond	5-20R
TR20USBACNI	Spec Grd - A/C	20	125	Nickel	5-20R
TR20USBACRED	Spec Grd - A/C	20	125	Red	5-20R
TR20USBACW	Spec Grd - A/C	20	125	White	5-20R



# Specification Grade USB Type-C/Type-C Chargers with Duplex Tamper-Resistant Receptacles

Catalog Number	Description	Ratir A	ng V	Color	NEMA Config. No.
TR15USBCC	Spec Grd - C/C	15	125	Brown	5-15R
TR15USBCCBK	Spec Grd - C/C	15	125	Black	5-15R
TR15USBCCGRY	Spec Grd - C/C	15	125	Grey	5-15R
TR15USBCCI	Spec Grd - C/C	15	125	lvory	5-15R
TR15USBCCLA	Spec Grd - C/C	15	125	Light Almond	5-15R
TR15USBCCW	Spec Grd - C/C	15	125	White	5-15R
TR20USBCC	Spec Grd - C/C	20	125	Brown	5-20R
TR20USBCCBK	Spec Grd - C/C	20	125	Black	5-20R
TR20USBCCGRY	Spec Grd - C/C	20	125	Grey	5-20R
TR20USBCCI	Spec Grd - C/C	20	125	lvory	5-20R
TR20USBCCLA	Spec Grd - C/C	20	125	Light Almond	5-20R
TR20USBCCNI	Spec Grd - C/C	20	125	Nickel	5-20R
TR20USBCCRED	Spec Grd - C/C	20	125	Red	5-20R
TR20USBCCW	Spec Grd - C/C	20	125	White	5-20R





SF20277 — August 2018 — For latest specs visit www.legrand.us/passandseymour

3



## Hospital Grade USB Type-A/Type-C Chargers with Duplex Tamper-Resistant Receptacles

Catalog Number	Description	Rating A	<sup>g</sup> v	Color	NEMA Config. No.
TR15HUSBAC	Hosp Grd - A/C	15	125	Brown	5-15R
TR15HUSBACBK	Hosp Grd - A/C	15	125	Black	5-15R
TR15HUSBACGRY	Hosp Grd - A/C	15	125	Grey	5-15R
TR15HUSBACI	Hosp Grd - A/C	15	125	lvory	5-15R
TR15HUSBACRED	Hosp Grd - A/C	15	125	Red	5-15R
TR15HUSBACW	Hosp Grd - A/C	15	125	White	5-15R
TR20HUSBAC	Hosp Grd - A/C	20	125	Brown	5-20R
TR20HUSBACBK	Hosp Grd - A/C	20	125	Black	5-20R
TR20HUSBACGRY	Hosp Grd - A/C	20	125	Grey	5-20R
TR20HUSBACI	Hosp Grd - A/C	20	125	lvory	5-20R
TR20HUSBACLA	Hosp Grd - A/C	20	125	Light Almond	5-20R
TR20HUSBACRED	Hosp Grd - A/C	20	125	Red	5-20R
TR20HUSBACW	Hosp Grd - A/C	20	125	White	5-20R



# Hospital Grade USB Type-C/Type-C Chargers with Duplex Tamper-Resistant Receptacles

Catalog Number	Description	Rating A	v	Color	NEMA Config. No.
TR15HUSBCC	Hosp Grd - C/C	15	125	Brown	5-15R
TR15HUSBCCBK	Hosp Grd - C/C	15	125	Black	5-15R
TR15HUSBCCGRY	Hosp Grd - C/C	15	125	Grey	5-15R
TR15HUSBCCI	Hosp Grd - C/C	15	125	lvory	5-15R
TR15HUSBCCRED	Hosp Grd - C/C	15	125	Red	5-15R
TR15HUSBCCW	Hosp Grd - C/C	15	125	White	5-15R
TR20HUSBCC	Hosp Grd - C/C	20	125	Brown	5-20R
TR20HUSBCCBK	Hosp Grd - C/C	20	125	Black	5-20R
TR20HUSBCCGRY	Hosp Grd - C/C	20	125	Grey	5-20R
TR20HUSBCCI	Hosp Grd - C/C	20	125	lvory	5-20R
TR20HUSBCCLA	Hosp Grd - C/C	20	125	Light Almond	5-20R
TR20HUSBCCRED	Hosp Grd - C/C	20	125	Red	5-20R
TR20HUSBCCW	Hosp Grd - C/C	20	125	White	5-20R



NEMA NEMA 5-15R 5-20R

SF20277 — August 2018 — For latest specs visit www.legrand.us/passandseymour



### **PASS & SEYMOUR®**

Specification & Hospital Grade USB Chargers 15 & 20A, 125V

#### **Vertical Markets**

- Healthcare Education · Retail Airports Hospitality/Lodging Multiple Dwelling · Office Institutional Also available Flexcor<sup>®</sup> Wire SPD & Isolated Straight Blade Weatherproof **Ground Devices** 
  - Ground Continuity Monitoring (GCM)
- **Plugs & Connectors**  Turnlok<sup>®</sup> Locking Devices
- **Boxes & Covers**
- · IEC 309 **Industrial Products**
- **Mesh Grips**
- Bulk Solutions

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us 905.738.9195 www.legrand.ca

