


Pass & Seymour

Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V


TR5251, TR5351

Rugged construction plus tamperresistance equals one safe receptacle

amper-resistant child safety outlets that conform to 2008 NEC® Article 406.11 are now available as a specification grade single receptacle. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Tri-drive mounting and backed out terminal screws combine to save installation time.



Features & Benefits



Field Uses/Vertical Markets

■ Retail ■ Office ■ Hospitality/Lodging ■ Multiple Dwelling



Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V

Ordering Information

| Catalog | Rating | | | NEMA | | |
|-------------------------------------|--------|-----|--------------|-------------|--|--|
| Number | A. | V. | Color | Config. No. | | |
| Single Receptacles Back & Side Wire | | | | | | |
| TR5251-I | 15 | 125 | Ivory | 5-15R | | |
| TR5251-W | 15 | 125 | White | 5-15R | | |
| TR5251 | 15 | 125 | Brown | 5-15R | | |
| TR5251-LA | 15 | 125 | Light Almond | 5-15R | | |
| TR5351-I | 20 | 125 | Ivory | 5-20R | | |
| TR5351-W | 20 | 125 | White | 5-20R | | |
| TR5351-LA | 20 | 125 | Light Almond | 5-20R | | |





NEMA 5-15F

5-20R


Straight Blade Receptacles Construction Grade Single Tamper-Resistant 15 & 20A, 125V



Technical Specifications


3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; Federal Specification WC596; CSA Certified, Standard CSA-C22.2 No. 42.



| Materials | | | |
|----------------------------------|-------------------------------|--|-----------------------------------|
| Face Back Body | Nylon PVC | Terminal Screws Hex Head Grounding Screw | Tri-Drive Brass Tri-Drive Zinc |
| Contacts ' | .032 (.8) Brass .080 Steel | | Plated Steel |
| Clamping Plate Mounting Strap | .042 Steel | Assembly Rivets Mounting Screws | Steel Tri-Drive Steel |





Dimensions for 15 & 20 Amp

Warranty

1Year

Complementary Devices & Accessories



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade



PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- ScrewlessPolycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Lighting & Fan Controls
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok®
 Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

www.legrand.ca



Legrand/Pass & Seymour P.O. Box 4822

Syracuse, NY 13221-4822 800-223-4185 North America Headquarters 60 Woodlawn Street

West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472) Fax: 1.860.232.2062 www.legrand.us **Legrand Canada** 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721