


PASS & SEYMOUR® Smart Wi-Fi, Tru-Universal In-Wall Dimmer



Conveniently dim your lights from anywhere

WWRL50xx

Conveniently control your lights and power from anywhere using the Legrand Smart Lights mobile app, Amazon Alexa, the Google Assistant, and other popular control platforms. In the app, use Scenes to create the perfect ambiance in your home. With automated schedules, sync your outdoor lights with sunrise and sunset, or program to simulate occupancy while you're away. Legrand dimmers also use less energy than ordinary switches, with automated options available to promote enhanced energy savings.

Ideal for residential and light commercial applications, the Smart Tru-Universal Dimmer, Wi-Fi is the simple solution to all your customers' dimming challenges.



FEATURES & BENEFITS

- Simple Calibration via android and iOS apps allows users to set the dimmer to virtually any 120V dimmable load
- Convenient operation combines On/Off Decorator switch
- Touch rocker for simple dimming operation
- Preset, Single-Pole and 3-Way operation
- Sleek, ergonomic design that matches today's styles
- Works with iOS and Android smart phones for control while at home or halfway around the world
- White LED locator light glows when device is off for easy location in the dark
- Works with virtually any dimmable lamp and load on typical residential and light commercial wiring (with the exception of 0-10V LED drivers)

COMPLIANCE



cULus Listed, UL1472, CSA-C22.2 No. 184.1-95. Conforms to NEMA WD-1 and WD-6. FCC Class B Part 15, IC. Works with Alexa Works with the Google Assistant, OCF Certified, Wi-Fi Certified.



RoHS Compliant.



PASS & SEYMOUR®


Smart Wi-Fi, Tru-Universal In-Wall Dimmer

ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION	RATING	NEMA	COMPLIANCE	COLORS	C00
WWRL50WHCCV2	Smart Tru-Universal Dimmer, Wi-Fi. Preset Single-Pole & 3-Way up to 50 Feet with HMR Remote	Fwd: 700W Inc/ELV 4.5A EFL/CFL/LED 500VA MLV REV. 450W INC/ELV 2.1A EFL/CFL/LED	120 VAC, 60Hz	CU INTER UNTER	White	China
WWRL50LACCV2	Smart Tru-Universal Dimmer, Wi-Fi. Preset Single-Pole & 3-Way up to 50 Feet with HMR Remote	Fwd: 700W Inc/ELV 4.5A EFL/CFL/LED 500VA MLV REV. 450W INC/ELV 2.1A EFL/CFL/LED	120 VAC, 60Hz	c (B) IS LISTER	Light Almond	China
WWRL50NICCV2	Smart Tru-Universal Dimmer, Wi-Fi. Preset Single-Pole & 3-Way up to 50 Feet with HMR Remote	Fwd: 700W Inc/ELV 4.5A EFL/CFL/LED 500VA MLV REV. 450W INC/ELV 2.1A EFL/CFL/LED	120 VAC, 60Hz	c (B) IS LISTER	Nickel	China
HMRTC	Multi-Location Remote Single-Pole, 3-Way	N/A	120VAC, 60Hz	CUU USTED	lvory, White, Light Almond	China
HMRW	Multi-Location Remote Single-Pole, 3-Way	N/A	120VAC, 60Hz	C US LISTED	White	China
HMRKITLA	Multi-Location Remote Dimmer, Interchangeable Faceplate	N/A			Light Almond	China
HMRKITNI	Multi-Location Remote Dimmer, Interchangeable Faceplate	N/A			Nickel	China
HMRKITW	Multi-Location Remote Dimmer, Interchangeable Faceplate	N/A		CUUUS LISTED	White	China

COMPATIBILITY

IC



DOWNLOAD THE APP



Smart Light

Download the iOS Legrand app



Download the Google Legrand app

PASS & SEYMOUR®

Smart Wi-Fi, Tru-Universal In-Wall Dimmer



1.77

8

WWRL50WH

1.53".

4.17"

2.60"

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, UL1472, CSA-C22.2 No. 184.1-95.

Conforms to NEMA WD-1 and WD-6. FCC Class B Part 15, IC. Works with Alexa Works with the Google Assistant, OCF Certified, Wi-Fi Certified.

Performance			
ELECTRICAL			
Supply Voltage	120 VAC		
Maximum Rated Load	FWD:700W INC/ELV, 4.5A EFL/CFL/LED, 500VA MLV REV: 450W INC/ELV, 2.1A EFL/CFL/LED		
Frequency	60Hz		
Installation	Single-Pole or 3-Way		
MECHANICAL			
Enclosure Material	Indoor Use Only		

Materials			
Paddle	Polycarbonate	Termination	6" long, 14 AWG, 105C 600V stranded wires
Back Body	Polycarbonate		

Арр

Android Requirements Apple IOS Requirements

Android 5.0 or higher with camera iOS 10.0 or higher with camera

Radio

Wi-Fi

Certified IEEE 802.11 b/g/n Wi-Fi 2.4GHz radio. Supports IPv4 and IPv6 addressing.

Warranty Limited Lifetime Warranty

VERTICAL MARKETS

Residential





Smart Wi-Fi, Tru-Universal In-Wall Dimmer

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

NOTE: The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.



Legrand, North America

60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

Canada 905.738.9195 www.legrand.ca

