



PlugTail® Connectors, Right Angle with WAGO Connector, Solid, 6-inch



## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                   |                |                    |              |
|-------------------|----------------|--------------------|--------------|
| Product Line      | Pass & Seymour | UPC Number         | 785007278248 |
| Country Of Origin | Mexico         | Application Sector | Commercial   |
| Standard          | cULus UL498    |                    |              |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                     |                          |                 |   |
|---------------------|--------------------------|-----------------|---|
| Dielectric Strength | Withstands 2000V minimum | Number of Wires | 3 |
|---------------------|--------------------------|-----------------|---|

---

|                    |   |                          |                       |
|--------------------|---|--------------------------|-----------------------|
| Temperature Rating | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact | Number of Poles          | Double Pole           |
| Wire Size          | PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only   | Environmental Conditions | Flammability: UL94 V2 |

---